

8000 A SB Zyklus ratchet with 1/4" drive, 1/4 inch x 152.0 mm

The Zyklus Ratchets, 1/4"



Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklus_ratchets_1_4_8000_a_sb_sis.html

Wera - 8000 A SB

05073260001 - 4013288128034

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

8000 A SB Zyklus ratchet with 1/4" drive, 1/4 inch x 152.0 mm

The Zyklus Ratchets, 1/4"



Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklus_ratchets_1_4_8000_a_sb_sis.html

Wera - 8000 A SB

05073260001 - 4013288128034

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

The Zyklop Ratchets, 1/4"

EAN/GTIN:	4013288128034	Dimension:	152x35x35 mm
Part no.:	05073260001	Weight:	147 g
Article no.:	8000 A SB	Country of origin:	CZ
		Customs tariff number:	82041100

- Fine-tooth design allows a small return angle of 5°
- Freely pivoting ratchet head, push button release and left/right switchover
- Flywheel design and easy-to-grip free-turning sleeve for very high working speeds
- The Wera Zyklop Speed ratchet combines the advantages of five different types of ratchet in one. And it is a really fast mover.
- Can also be used as a screwdriver

Zyklop ratchet with 1/4" drive. The 72 fine-pitched teeth result in the ratchet having a very small return angle of only 5°. The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90° both to the left and right ensures safe working without any slipping of the ratchet head. The ratchet can be used as a conventional screwdriver in its 0° position by attaching an adaptor and bit. The flywheel design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process. The outstanding design of the Kraftform handle fits perfectly into the hand, preventing injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle. The softer anti-slip zones enable the low-loss transfer of high forces. Suitable for 1/4" square sockets as well as 1/4" adaptor with square drive; with ball lock.

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklop_ratchets_1_4_8000_a_sb_sis.html

Wera - 8000 A SB
05073260001 - 4013288128034

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The Zyklop Ratchets, 1/4"

Content:



8000 A

05003500001 1 x 1/4"x152.0



Zyklop "6 in 1"



Incredibly fast 1/4" Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely



The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers




The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

Ball lock



The ball lock holds the sockets and attachments securely, ensuring safe working. A changeover into any predefined position is completed by simply pressing the release button – this is even the case in the 90° position.

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklop_ratchets_1_4_8000_a_sb_sis.html

Wera - 8000 A SB

05073260001 - 4013288128034

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de