



EAN/GTIN: 4013288093493
Part no.: 05030151001
Article no.: 1569 ESD

Dimension: 157x13x13 mm
Weight: 22 g
Country of origin: CZ
Customs tariff number: 82054000



- ESD nutsetter for hexagon head screws
- ESD-safe tool thanks to surface resistance of $< 10^9 \Omega$
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Anti-roll feature and swivel cap for rapid twisting
- Rapid twisting possible

ESD-safe Micro nutsetter for hexagon head screws. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work.

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_screwdrivers_esd_series_1569_esd.html

Wera - 1569 ESD
05030151001 - 4013288093493

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

Kraftform Micro Handle




Multi-component screwdriver handle for ergonomic working.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_screwdrivers_esd_series_1569_esd.html

Wera - 1569 ESD
05030151001 - 4013288093493

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

More variants of this product family:

		 mm	 mm	 mm	 inch
05030410001	1.5	60	97	5.7	2 3/8
05030411001	1.8	60	97	5.7	2 3/8
05030412001	2.0	60	97	5.7	2 3/8
05030413001	2.5	60	97	5.7	2 3/8
05030414001	3.0	60	97	5.7	2 3/8
05030415001	3.2	60	97	5.7	2 3/8
05030416001	3.5	60	97	5.7	2 3/8
05030417001	4.0	60	97	5.7	2 3/8
05030418001	4.5	60	97	6.4	2 3/8
05030150001	5.0	60	97	7.0	2 3/8
05030151001	5.5	60	97	7.8	2 3/8

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_screwdrivers_esd_series_1569_esd.html

Wera - 1569 ESD

05030151001 - 4013288093493

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de