

300 Hex torque-indicator, pistol grip, Hex-Plus, 4.0 mm, 5.0 Nm

Series Torque-indicators



EAN/GTIN: 4013288099150
Part no.: 05027913001
Article no.: 300 Hex Pistole

Dimension: 218x81x51 mm
Weight: 219 g
Country of origin: CZ
Customs tariff number: 82054000

- Torque -indicator with pre-set and tamperproof torque value
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Non-adjustable and tamperproof
- Unlimited torque for loosening seized screws
- Multi-component Kraftform pistol handle for fast and ergonomic screwdriving

Wera torque screwdriver with fixed torque for hexagon socket screws. Tamperproof and with a slim hex blade. Unlimited torque for loosening seized screws. Multi-component Kraftform handle for pleasant, ergonomic working that prevents blisters and calluses. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.

Weblink

http://products.wera.de/en/torque_tools_series_torque-indicators_300_hex_pistole.html

Wera - 300 Hex Pistole
05027913001 - 4013288099150

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series Torque-indicators

Torque-indicators




Wera torque-indicators have been factory pre-set to values recommended by leading carbide tool manufacturers. These tightening values relate specifically to the size of the TORX®, TORX PLUS® or hexagon socket screw. Torque indicators ensure safe and easy loosening of screw connections. Precision : ± 10 %

Torque-indicators




Suitable for applications requiring a non-adjustable i.e. a tamperproof torque blade assembly.

Torque-indicators




Some screw connections require specific torque values so that they can be tightened or loosened easily. Wera torque-indicators are pre-set to torque values recommended by leading carbide tool manufacturers. Pre-set torque between 0.6 Nm and 5.0 Nm, for TORX®, TORX PLUS® and hexagon socket screws, unlimited loosening torque, two handles, tamper-proof.

Precisely adjusted



Torque blade assembly precisely adjusted to the respective screw size for the TORX®, TORX PLUS® and hexagon socket screw profiles.

For difficult-to-access places




Slim 4 mm hexagon blades to reach screws in difficult-to-access places.

Tamperproof



Non-adjustable and tamperproof.

Excess-load signal





Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Kraftform handle



Multi-component Kraftform handle with hard and soft zones for fast working speeds and protecting the palm of the hand.

More variants of this product family:



05027913001	4.0	160	100	65	2 9/16	25	1
-------------	-----	-----	-----	----	--------	----	---

Weblink

http://products.wera.de/en/torque_tools_series_torque-indicators_300_hex_pistole.html

Wera - 300 Hex Pistole
05027913001 - 4013288099150

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de