

## 800/9 C bits, 0.40 x 2.0 x 44 mm

### Bits for Slotted Screws



<b>EAN/GTIN:</b>	4013288168283	<b>Dimension:</b>	44x4x4 mm
<b>Part no.:</b>	05135266001	<b>Weight:</b>	3 g
<b>Article no.:</b>	800/9 C	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- For slotted screws
- Hard design
- 4 mm halfmoon drive (Wera connecting series 9)
- Suitable for Delvo, Densei, etc.

Hard bits against premature breakage. Drive: halfmoon, 4 mm.

#### Weblink


[http://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_wera\\_bits\\_bits\\_for\\_slotted\\_screws\\_800\\_9\\_c.html](http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_slotted_screws_800_9_c.html)

Wera - 800/9 C  
05135266001 - 4013288168283

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)






## Bits for Slotted Screws

## 4 mm Halfmoon direct drive



Halfmoon, 4mm, Wera Series 9.  
 Drive: For direct machine drive.  
 Suitable for: Delvo, Densei etc.

## More variants of this product family:

	 mm	 mm	 mm	 inch	 mm
05135265001	0.23	1.5	44	1 47/64	1.5
05135264001	0.35	2.5	44	1 47/64	2.5
<b>05135266001</b>	<b>0.40</b>	<b>2.0</b>	<b>44</b>	<b>1 47/64</b>	<b>2.0</b>
05135267001	0.50	3.0	44	1 47/64	3.0

## Weblink

[http://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_wera\\_bits\\_bits\\_for\\_slotted\\_screws\\_800\\_9\\_c.html](http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_slotted_screws_800_9_c.html)

Wera - 800/9 C

05135266001 - 4013288168283

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)