



EAN/GTIN:	4013288112897	Dimension:	60x5x4 mm
Part no.:	05135291001	Weight:	7 g
Article no.:	851/21 J	Country of origin:	CZ
		Customs tariff number:	82079030

- For Phillips screws
- Hard design
- Optimised for Japanese Phillips screws
- 4 mm HIOS drive (Wera connecting series 21)
- Suitable for BL-5000, CL-2000, CL-3000, CL-4000, SS-3000, SS-4000 etc.

High quality bits with HIOS 4 mm drive. Optimised for Japanese PH screws. Hard design.

Weblink


http://products.wera.de/en/bits HOLDERS_adaptors_the_range_of_wera_bits_bits_for_phillips_screws_851_21_j.html

Wera - 851/21 J
05135291001 - 4013288112897

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Phillips Screws

4 mm HIOS direct drive



HIOS, 4mm, Wera Series 21.
 Drive: For direct machine drive.
 Suitable for: BL-5000, CL-2000,
 CL-3000, CL-4000, SS-3000,
 SS-4000, L-4500, L-5000,
 CD-4000, CD-5000, VZ-1510
 (incl. PS-type).

More variants of this product family:

				
		mm	inch	mm
05135280001 ¹⁾	PH 00	40	1 9/16	1.8
05135281001 ¹⁾	PH 00	60	2 3/8	1.8
05135284001 ²⁾	PH 0	40	1 9/16	1.8
05135285001 ²⁾	PH 0	60	2 3/8	1.8
05135286001 ²⁾	PH 0	40	1 9/16	2.0
05135287001 ²⁾	PH 0	60	2 3/8	2.0
05135288001 ²⁾	PH 0	40	1 9/16	2.5
05135289001 ²⁾	PH 0	60	2 3/8	2.5
05135290001	PH 1	40	1 9/16	3.0
05135291001	PH 1	60	2 3/8	3.0

1) Size 00 modified according to JCS 00 (Japanese Camera Industrial Standard)

2) Size 0 modified according to JCS 0 (Japanese Camera Industrial Standard)

Weblink

http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_phillips_screws_851_21_j.html

Wera - 851/21 J

05135291001 - 4013288112897

Wera Werkzeuge GmbH
 Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de