


8001 A Bit Ratchet 1/4" SB with 1/4" drive, 2 pieces

Zyklop Mini



EAN/GTIN:	4013288144638	Dimension:	180x60x16 mm
Part no.:	05073230001	Weight:	126 g
Article no.:	8001 A SB	Country of origin:	TW
		Customs tariff number:	82041100

- Suitable for direct take-up of bits with 1/4" hex head drive
- Drop-forged, full-steel design
- Torque of over 65 Nm
- Fine-pitched ratchet mechanism and small return angle of 6°
- Ideal for working in confined spaces

The Wera Mini ratchet. Simple operation, even with just one hand, in confined working spaces. Drop-forged, full-steel design and fine-pitched mechanism with 60 teeth that allows a small return angle of 6° for precise working. The thumbwheel allows rapid fastening in confined situations when there is no space for ratcheting. Easy left/right switchover. Ergonomically designed ratchet head and lever. Suitable for 1/4" bit and socket take-up.

Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_zyklop_mini_8001_a_sb.html

Wera - 8001 A SB
05073230001 - 4013288144638

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop Mini

Content:



8001 A

05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0
05073999001	1 x 1/4"x87.0



870/1

05136000001 ¹⁾	1 x 1/4"x25
---------------------------	-------------

1) With friction ball; for manual nut spinner sockets

The Zyklop Mini Ratchets




Combines elegant design with incredible resilience. Suitable for rapid fastening even in confined working situations. The Wera Zyklop Mini is applied whenever fastening with a power tool or conventional tools is impossible due to insufficient space. The Zyklop Mini 1 for the direct attachment of bits; the Zyklop Mini 2 for the direct attachment of the special Wera Zyklop sockets.




For all difficult-to-access applications.

Small return angle



The fine tooth mechanism, with its 60 teeth, allows a small return angle of only 6° – ideal for precision work.

Rapid screwdriving



Thumbwheel enables rapid screwdriving, even when there isn't sufficient room for ratcheting use.

Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_zyklop_mini_8001_a_sb.html

Wera - 8001 A SB
05073230001 - 4013288144638

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop Mini

Simple direction change



Simple switching between left/right operations.

Slim design



Its slim design makes it ideal for all particularly confined working situations.

Is such a small tool sufficiently resilient?



The Zyklop Mini 1 can withstand at least 65 Nm. That is far more power than can normally be transferred to such a small tool.

What parts can be connected to the Zyklop Mini 1?



Bits and sockets. Bits can be connected directly. However, a holder can be connected first and then the bit can be attached to this. This then serves as an extension with a free-turning sleeve. An adaptor e.g. Wera 870/1 is needed for sockets – ¼" hexagonal on a square drive (included in the Bit-Check and with the individual Zyklop Mini 1 in the set).

Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_zyklop_mini_8001_a_sb.html

Wera - 8001 A SB
05073230001 - 4013288144638

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de