

Bits for TORX® Screws



EAN/GTIN:	4013288037107	Dimension:	70x4x4 mm
Part no.:	05332607001	Weight:	6 g
Article no.:	867/9 C TORX®	Country of origin:	CZ
		Customs tariff number:	82079030

- For recessed TORX® screws
- Hard design
- 4 mm halfmoon drive (Wera connecting series 9)
- Suitable for Delvo, Densei, etc.
- Direct power tool insertion

Hard bits for recessed TORX® screws. Drive: 4 mm halfmoon for direct power tool connection.

Weblink


http://products.wera.de/en/bits HOLDERS_adaptors_the_range_of_wera_bits_bits_for_torx_screws_867_9_c_torx.html

Wera - 867/9 C TORX®
05332607001 - 4013288037107

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for TORX® Screws

4 mm Halfmoon direct drive



Halfmoon, 4mm, Wera Series 9.
 Drive: For direct machine drive.
 Suitable for: Delvo, Densei etc.

More variants of this product family:

		 mm	 inch	 mm
05135220001	TX 1	44	1 47/64	1.5
05135221001	TX 2	44	1 47/64	1.5
05135222001	TX 3	44	1 47/64	1.7
05345352001	TX 4	44	1 47/64	1.8
05345018001	TX 4	64	2 33/64	2.0
05345351001	TX 5	44	1 47/64	3.0
05345032001	TX 5	64	2 33/64	2.0
05314753001	TX 5	70	2 3/4	2.0
05345350001	TX 6	44	1 47/64	3.0
05345056001	TX 6	64	2 33/64	2.0
05332610001	TX 6	70	2 3/4	3.0
05345035001	TX 7	64	2 33/64	2.3
05345026001	TX 8	44	1 47/64	3.0
05345028001	TX 8	64	2 33/64	3.0
05332609001	TX 8	70	2 3/4	3.0
05332607001	TX 10	70	2 3/4	3.0

Weblink

http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_torx_screws_867_9_c_torx.html

Wera - 867/9 C TORX®
 05332607001 - 4013288037107

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de