



EAN/GTIN: 4013288108128
Part no.: 05008750001
Article no.: 350 SK PH

Dimension: 141x26x26 mm
Weight: 33 g
Country of origin: CZ
Customs tariff number: 82054000



- Screwdriver for cross-recess screws, Phillips
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- "Take it easy" Tool Finder: colour coding according to profile and size
- Hexagonal blade and bolster for higher torque transfer
- Chrome-plated

High quality Kraftform Plus screwdriver with hexagonal blade. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer for fast and low-fatigue working. "Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool. The hexagonal non-roll feature prevents any rolling away at the workplace.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus__series_300_350_sk_ph.html


Wera - 350 SK PH
05008750001 - 4013288108128

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Lasertip prevents slipping out



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally “bites” itself firmly into the screw head. Slipping out becomes a thing of the past.

Lasertip



A precisely-focused laser creates a sharp-edged surface structure. This laser treatment results in an edge hardness of up to 1000 HV 0.3. Wera Lasertip “bites” itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer – meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_350_sk_ph.html

Wera - 350 SK PH
05008750001 - 4013288108128

Hexagonal blade and bolster for higher torque transfer.



Hexagonal blade and bolster for higher torque transfer.

Kraftform




The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Prevents hand injuries









The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

“Take it easy” Toolfinder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

More variants of this product family:

						
		mm	mm	mm	mm	inch
05008750001 ¹⁾	PH 0	4		60	81	2 3/8
05008751001	PH 1	5	8	80	98	3 1/8
05008752001	PH 2	6	10	100	105	4
05008753001	PH 3	8	13	150	112	6

¹⁾ without Lasertip

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_350_sk_ph.html

Wera - 350 SK PH
05008750001 - 4013288108128

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de