

391 Hose clamp screwdriver, 6.0 mm x 167 mm

Kraftform Plus – Series 300



EAN/GTIN:	4013288004703	Dimension:	265x33x33 mm
Part no.:	05028148001	Weight:	114 g
Article no.:	391	Country of origin:	CZ
		Customs tariff number:	82054000

- Hose clamp screwdriver for hexagon head screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Hexagonal anti-roll feature against rolling away
- Flexible, circular blade
- Handle markings simplify finding and sorting of tools

High quality hose clamp screwdriver by Wera. Multi-component Kraftform handle for high working speeds and particularly ergonomic screwdriving. Kraftform Plus: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Flexible blade for reaching difficult-to-access places. Hexagonal anti-roll prevents any rolling away and handle markings make for simplified finding and sorting of the tool.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus__series_300_391.html

Wera - 391
05028148001 - 4013288004703

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Flexible shaft



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



Screwdriving can also be achieved “around the corner” with the screwdriver 391. The flexible shaft allows unfavourably-positioned screw fastenings to be reached. The ideal tool for difficult-to-access screwdriving applications e.g. in the engine compartment of a car.

Kraftform



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin “sticking” to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

Large contact area



The large contact area – with particularly high friction to the soft zones – results in high torque transfer without any bruising from the edges.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case or at the workplace.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_391.html

Wera - 391
05028148001 - 4013288004703





Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

391 Hose clamp screwdriver, 6.0 mm x 167 mm

Kraftform Plus – Series 300



More variants of this product family:

	 mm	 mm	 mm	 inch
05028148001	6	167	98	6 9/16
05028150001	7	167	98	6 9/16
05028152001	8	167	98	6 9/16

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_391.html

Wera - 391

05028148001 - 4013288004703

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de