

## 336 Stubby/Carburettor screwdriver, 0.8 x 4.0 x 25 mm

Kraftform Plus – Series 300



|                     |               |                               |             |
|---------------------|---------------|-------------------------------|-------------|
| <b>EAN/GTIN:</b>    | 4013288037022 | <b>Dimension:</b>             | 79x34x34 mm |
| <b>Part no.:</b>    | 05110069001   | <b>Weight:</b>                | 29 g        |
| <b>Article no.:</b> | 336 Stubby    | <b>Country of origin:</b>     | CZ          |
|                     |               | <b>Customs tariff number:</b> | 82054000    |

- Stubby/Carburettor screwdriver for slotted screws
- Single-component Kraftform handle
- Hexagonal anti-roll feature against rolling away
- Extra-short circular blade
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

Particularly small screwdrivers for difficult-to-access areas. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace. The Wera Black Point tip and a complex hardening process ensure a long service life of the tip, enhanced corrosion protection and an exact fit.

### Weblink

[http://products.wera.de/en/screwdrivers\\_kraftform\\_plus\\_series\\_300\\_336\\_stubby.html](http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_336_stubby.html)

Wera - 336 Stubby  
05110069001 - 4013288037022








Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

## More variants of this product family:

|                    |  |  |  |  |  |  |  |
|--------------------|---|---|---|---|---|---|---|
|                    | mm  | mm  | mm  | mm  | mm  | inch  | inch  |
| 05110068001        | 0.6   | 3.5   | 25  | 54  | 3.5   | 9/64  | 1   |
| <b>05110069001</b> | <b>0.8</b>  | <b>4.0</b>  | <b>25</b>   | <b>54</b>   | <b>4.0</b>  | <b>5/32</b>   | <b>1</b>  |
| 05110070001        | 1.0   | 5.5   | 25  | 54  | 5.5   | 7/32  | 1   |
| 05110075001        | 1.2   | 6.5   | 25  | 54  | 6.5   | 1/4   | 1   |
| 05110078001        | 1.2   | 8.0   | 25  | 54  | 8.0   | 5/16  | 1   |

## Weblink

[http://products.wera.de/en/screwdrivers\\_kraftform\\_plus\\_series\\_300\\_336\\_stubby.html](http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_336_stubby.html)

Wera - 336 Stubby  
 05110069001 - 4013288037022

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de