

Series Kraftform Micro



| | | | |
|---------------------|---------------|-------------------------------|--------------|
| EAN/GTIN: | 4013288110954 | Dimension: | 157x13x13 mm |
| Part no.: | 05118106001 | Weight: | 19 g |
| Article no.: | 2052 Micro | Country of origin: | CZ |
| | | Customs tariff number: | 82054000 |



- Kraftform Micro screwdriver with ballpoint for hexagon socket screws
- Multi-component Kraftform Micro handle with anti-roll feature and swivel cap
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Ballpoint for dependable working even in difficult installation situations
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

High quality Wera Micro screwdriver for precision mechanical work. Ballpoint profile: the ballpoint drive profile means that it is possible to swivel the tool axis away from the screwdriving axis, thus enabling "round the corner" screwdriving. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit.

Weblink
http://products.wera.de/en/screwdrivers_series_kraftform_micro_2052_micro.html

Wera - 2052 Micro
 05118106001 - 4013288110954


Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Series Kraftform Micro

Ball tip




Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision – and we then focused particularly on these issues.



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, “around-the-corner” screwdriving jobs.

Kraftform Micro Handle



Multi-component screwdriver handle for ergonomic working.

The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.







Weblink

http://products.wera.de/en/screwdrivers_series_kraftform_micro_2052_micro.html

Wera - 2052 Micro
05118106001 - 4013288110954

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

More variants of this product family:

| |  |  |  |  |  |  |
|--------------------|---|---|---|--|---|---|
| | mm | inch | mm | mm | mm | inch |
| 05118089001 | 1.3 | - | 60 | 97 | 3.0 | 2 3/8 |
| 05118090001 | 1.5 | - | 60 | 97 | 3.0 | 2 3/8 |
| 05118092001 | 2.0 | - | 60 | 97 | 3.0 | 2 3/8 |
| 05118094001 | 2.5 | - | 60 | 97 | 4.0 | 2 3/8 |
| 05118096001 | 3.0 | - | 60 | 97 | 4.0 | 2 3/8 |
| 05118098001 | - | 1/16 | 60 | 97 | 3.0 | 2 3/8 |
| 05118100001 | - | 5/64 | 60 | 97 | 3.0 | 2 3/8 |
| 05118102001 | - | 3/32 | 60 | 97 | 3.0 | 2 3/8 |
| 05118106001 | - | 7/64 | 60 | 97 | 4.0 | 2 3/8 |
| 05118103001 | - | 1/8 | 60 | 97 | 4.0 | 2 3/8 |

Weblink

http://products.wera.de/en/screwdrivers_series_kraftform_micro_2052_micro.html

Wera - 2052 Micro

05118106001 - 4013288110954

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de