

## 80 RA Vario ratchet screwdriver, 6 x 115.0 mm

Kraftform Kompakt Vario with Ratchet Function.



<b>EAN/GTIN:</b>	4013288156242	<b>Dimension:</b>	189x64x38 mm
<b>Part no.:</b>	05002901001	<b>Weight:</b>	154 g
<b>Article no.:</b>	80 RA	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Vario ratcheting screwdriver for Wera 6 mm Vario blades
- Ratchet with fine-pitched toothing for a low return angle
- Switchover ring (right, fixed, left)
- Maximum torque of up to 50 Newton metres
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer

Ratchet, fine-pitched toothing for a low return angle, switchover ring (right, fixed, left), maximum torque of up to 50 Newton meters; 6 mm hexagon take-up. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.

### Weblink

[http://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_vario\\_with\\_ratchet\\_function\\_fine\\_tooth\\_system\\_for\\_precision\\_work\\_80\\_ra.html](http://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_vario_with_ratchet_function_fine_tooth_system_for_precision_work_80_ra.html)

Wera - 80 RA  
05002901001 - 4013288156242

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)


**Kraftform Kompakt Vario with Ratchet Function.**

**Fine-tooth design**



Fine action 44 tooth system for precision work. Great time savings when screwdriving.

**Changing ratchet direction**




Ergonomic design of the reverse direction switch.

**Fine adjustment work**



Additionally, the lockable neutral position permits exact adjustment work without having to change the screwdriving direction every time. Lockable neutral position for fine adjustment work.

**Handle/interchangeable blade system**



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

**Kraftform**



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

**Prevents hand injuries**



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

**Weblink**

[http://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_vario\\_with\\_ratchet\\_function\\_fine\\_tooth\\_system\\_for\\_precision\\_work\\_80\\_ra.html](http://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_vario_with_ratchet_function_fine_tooth_system_for_precision_work_80_ra.html)

Wera - 80 RA  
05002901001 - 4013288156242

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

# 80 RA Vario ratchet screwdriver, 6 x 115.0 mm

Kraftform Kompakt Vario with Ratchet Function.



More variants of this product family:



mm



mm

05002901001	6	115.0
-------------	---	-------

### Weblink

[http://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_vario\\_with\\_ratchet\\_function\\_fine\\_tooth\\_system\\_for\\_precision\\_work\\_80\\_ra.html](http://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_vario_with_ratchet_function_fine_tooth_system_for_precision_work_80_ra.html)

Wera - 80 RA

05002901001 - 4013288156242

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)