

Bits for TORX PLUS® Screws



EAN/GTIN:	4013288113511	Dimension:	64x4x4 mm
Part no.:	05345019001	Weight:	5 g
Article no.:	867/9 C TORX PLUS®	Country of origin:	CZ
		Customs tariff number:	82079030

- For TORX PLUS® screws
- Hard design
- 4 mm halfmoon drive (Wera connecting series 9)
- Suitable for Delvo, Densei, etc.
- Direct power tool insertion

Hard bits for recessed TORX PLUS® screws. Drive: 4 mm halfmoon for direct power tool insertion.

Weblink

http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_torx_plus_screws_867_9_c_torx_plus.html


Wera - 867/9 C TORX PLUS®
05345019001 - 4013288113511

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for TORX PLUS® Screws

TORX PLUS®

4 mm Halfmoon direct drive



Compared with the "normal" TORX® profile, the elliptical instead of circular profile enlarges the 6 flanks that transfer torque between the tool and the screw. This means that the force applied when screwdriving is spread across a larger surface area. Higher torque is transferred and, in addition, the service life of the screw and tool are lengthened. The so-called centre-lock screws on cutting tools represent a typical use of this type of screw profile. The thermal influences on such holders for carbide insert tips often "bake" the retaining screws so firmly that it is important to have a profile that considerably enhances the loosening torque capability of the screws. For this reason a torque-stable screw profile is necessary to avoid any possible damage to the screw and to exclude the possibility of an otherwise costly machine downtime.

Halfmoon, 4mm, Wera Series 9.
Drive: For direct machine drive.
Suitable for: Delvo, Densei etc.

Weblink

http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_torx_plus_screws_867_9_c_torx_plus.html

Wera - 867/9 C TORX PLUS®
05345019001 - 4013288113511

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for TORX PLUS® Screws

More variants of this product family:

						
		mm	inch	mm	mm	inch
05135230001	1 IP	44	1 47/64	1.5	20	25/32
05135231001	2 IP	44	1 47/64	1.5	20	25/32
05135232001	3 IP	44	1 47/64	1.7	20	25/32
05326310001	4 IP	44	1 47/64	2.0	20	25/32
05345019001	4 IP	64	2 33/64	2.0	20	25/32
05135233001	5 IP	44	1 47/64	2.0	20	25/32
05332612001	5 IP	70	2 3/4	3.0	20	25/32
05344900001	6 IP	44	1 47/64	2.25	20	25/32
05135234001	8 IP	44	1 47/64	3.0	20	25/32
05332606001	8 IP	70	2 3/4	3.0	20	25/32
05135235001	10 IP	44	1 47/64	3.0	20	25/32

Weblink

http://products.wera.de/en/bits_holders_adaptors_the_range_of_wera_bits_bits_for_torx_plus_screws_867_9_c_torx_plus.html

Wera - 867/9 C TORX PLUS®
 05345019001 - 4013288113511

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de