

335 Screwdriver for slotted screws, 0.5 x 3.0 x 80 mm

Kraftform Plus – Series 300



EAN/GTIN: 4013288003256
Part no.: 05110001001
Article no.: 335

Dimension: 161x26x26 mm
Weight: 28 g
Country of origin: CZ
Customs tariff number: 82054000



- Slotted screwdriver -electrician's blade
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- "Take it easy" Tool Finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Chrome-plated

High quality Kraftform Plus screwdriver with electrician's blade. Multi-component Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. "Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool. The hexagonal non-roll feature prevents any rolling away at the workplace.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_335.html


Wera - 335
05110001001 - 4013288003256

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Lasertip prevents slipping out



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally “bites” itself firmly into the screw head. Slipping out becomes a thing of the past.

Lasertip



A precisely-focused laser creates a sharp-edged surface structure. This laser treatment results in an edge hardness of up to 1000 HV 0.3. Wera Lasertip “bites” itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer – meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_335.html

Wera - 335

05110001001 - 4013288003256


Wera Werkzeuge GmbH
Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

“Take it easy” Toolfinder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

Kraftform



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin “sticking” to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_335.html

Wera - 335

05110001001 - 4013288003256

Wera Werkzeuge GmbH








Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

More variants of this product family:

| |  mm |  mm |  mm |  mm |  mm |  inch |  inch |
|---------------------------------|---|---|---|---|---|---|---|
| 05008006001 ¹⁾ | 0.4 | 2.0 | 60 | 70 | 2.5 | 5/64 | 2 3/8 |
| 05110000001 ¹⁾ | 0.4 | 2.5 | 60 | 70 | 2.5 | 3/32 | 2 3/8 |
| 05008007001 ¹⁾ | 0.4 | 2.5 | 75 | 70 | 2.5 | 3/32 | 3 |
| 05008008001 ¹⁾ | 0.5 | 3.0 | 150 | 81 | 4.0 | 1/8 | 6 |
| 05008009001 ¹⁾ | 0.5 | 3.0 | 200 | 81 | 4.0 | 1/8 | 8 |
| 05110001001¹⁾ | 0.5 | 3.0 | 80 | 81 | 3.0 | 1/8 | 3 1/8 |
| 05008015001 | 0.6 | 3.5 | 100 | 81 | 3.5 | 9/64 | 4 |
| 05110002001 | 0.6 | 3.5 | 125 | 81 | 3.5 | 9/64 | 5 |
| 05110003001 | 0.6 | 3.5 | 200 | 81 | 3.5 | 9/64 | 8 |
| 05110004001 | 0.8 | 4.0 | 100 | 98 | 4.0 | 5/32 | 4 |
| 05110005001 | 0.8 | 4.0 | 150 | 98 | 4.0 | 5/32 | 6 |
| 05110006001 | 0.8 | 4.0 | 200 | 98 | 4.0 | 5/32 | 8 |
| 05008027001 ¹⁾ | 0.8 | 4.0 | 300 | 98 | 4.0 | 5/32 | 12 |
| 05110007001 | 1.0 | 5.5 | 125 | 98 | 5.5 | 7/32 | 5 |
| 05008055001 | 1.0 | 5.5 | 150 | 98 | 5.5 | 7/32 | 6 |
| 05110008001 | 1.0 | 5.5 | 200 | 98 | 5.5 | 7/32 | 8 |
| 05008060001 ¹⁾ | 1.0 | 5.5 | 300 | 98 | 5.5 | 7/32 | 12 |
| 05008061001 | 1.2 | 6.0 | 100 | 105 | 6.0 | 5/16 | 4 |

1) without Lasertip

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_335.html

Wera - 335

05110001001 - 4013288003256

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de