

378 B Screwdriver for slotted screws, 1.6 x 10.0 x 200 mm

Kraftform Plus – Series 300



EAN/GTIN: 4013288004666
Part no.: 05110150001
Article no.: 378 B

Dimension: 312x40x40 mm
Weight: 204 g
Country of origin: CZ
Customs tariff number: 82054000



- Screwdriver for slotted screws
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- "Take it easy" Tool Finder: colour coding according to profile and size
- Square blade
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

High quality Kraftform Plus screwdriver. Multi-component Kraftform handle for high working speeds and particularly ergonomic screwdriving. Comes with square bolster for additional torque. "Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool. The hexagonal anti-roll feature prevents any bothersome rolling away.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_378_b.html

Wera - 378 B
05110150001 - 4013288004666

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Plus – Series 300

Kraftform



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Rapid hand repositioning




The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin “sticking” to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

Large contact area




The large contact area – with particularly high friction to the soft zones – results in high torque transfer without any bruising from the edges.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

“Take it easy” Toolfinder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.








Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_378_b.html

Wera - 378 B
05110150001 - 4013288004666

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

More variants of this product family:

	 mm	 mm	 mm	 mm	 mm	 inch	 inch
05110050001	0.8	4.0	4	75	98	5/32	3
05110051001	1.0	5.5	5	100	98	7/32	4
05110052001	1.2	6.5	6	125	105	1/4	5
05110053001	1.6	8.0	8	150	112	5/16	6
05007355001	1.6	10.0	8	60	112	3/8	2 3/8
05110054001	1.6	10.0	8	175	112	3/8	7
05110150001	1.6	10.0	8	200	112	3/8	8
05110055001	2.0	12.0	10	200	112	1/2	8
05110151001	2.0	12.0	10	250	112	1/2	10

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_378_b.html

Wera - 378 B

05110150001 - 4013288004666

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de