


367 TORX® Screwdriver for TORX® screws, TX 45 x 130 mm

Kraftform Plus – Series 300



EAN/GTIN: 4013288004291
Part no.: 05028025001
Article no.: 367 TORX®

Dimension: 242x40x40 mm
Weight: 146 g
Country of origin: CZ
Customs tariff number: 82054000



- Screwdriver for recessed TORX® screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- "Take it easy" Tool Finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

High quality Kraftform Plus screwdriver. Multi-component Kraftform handle for fast and low-fatigue working. Kraftform Plus: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. The Wera Black Point tip and a complex hardening process ensure a long service life of the tip, enhanced corrosion protection and an exact fit. "Take it easy" Tool Finder: colour coding according to profile and size. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_367_torx.html

Wera - 367 TORX®
05028025001 - 4013288004291

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Rapid hand repositioning




The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin “sticking” to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

Large contact area



The large contact area – with particularly high friction to the soft zones – results in high torque transfer without any bruising from the edges.

Non-roll feature




The hexagonal non-roll feature prevents any rolling away at the workplace.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case or at the workplace.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.






Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_367_torx.html

Wera - 367 TORX®
05028025001 - 4013288004291

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

More variants of this product family:

| |  |  mm |  mm |  mm |  inch |
|--------------------|---|---|---|---|---|
| 05028000001 | TX 5 | 60 | 70 | 3.5 | 2 3/8 |
| 05028001001 | TX 6 | 60 | 70 | 3.5 | 2 3/8 |
| 05028002001 | TX 7 | 60 | 70 | 3.5 | 2 3/8 |
| 05028003001 | TX 8 | 60 | 81 | 3.5 | 2 3/8 |
| 05028004001 | TX 9 | 60 | 81 | 4.0 | 2 3/8 |
| 05028005001 | TX 10 | 80 | 81 | 4.0 | 3 1/8 |
| 05028008001 | TX 15 | 80 | 98 | 4.0 | 3 1/8 |
| 05028010001 | TX 20 | 100 | 98 | 4.5 | 4 |
| 05028012001 | TX 25 | 100 | 105 | 5.0 | 4 |
| 05028013001 | TX 27 | 115 | 105 | 5.5 | 4 9/16 |
| 05028015001 | TX 30 | 115 | 105 | 6.0 | 4 9/16 |
| 05028020001 | TX 40 | 130 | 112 | 7.0 | 5 1/8 |
| 05028025001 | TX 45 | 130 | 112 | 8.0 | 5 1/8 |

Weblink

http://products.wera.de/en/screwdrivers_kraftform_plus_series_300_367_torx.html

Wera - 367 TORX®

05028025001 - 4013288004291

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de