

300 Hex torque-indicator, Hex-Plus, 2.5 mm, 2.0 Nm

Series Torque-indicators



EAN/GTIN:	4013288096432	Dimension:	170x37x37 mm
Part no.:	05027911001	Weight:	126 g
Article no.:	300 Hex	Country of origin:	CZ
		Customs tariff number:	82054000

- Torque -indicator with pre-set and tamperproof torque value
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Non-adjustable and tamperproof
- Unlimited torque for loosening seized screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving

Wera torque screwdriver with fixed torque for hexagon socket screws. Tamperproof and with a slim hex blade. Unlimited torque for loosening seized screws. Multi-component Kraftform handle for pleasant, ergonomic working that prevents blisters and calluses. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.

Weblink

http://products.wera.de/en/torque_tools_series_torque-indicators_300_hex.html

Wera - 300 Hex
05027911001 - 4013288096432

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Torque-indicators



Wera torque-indicators have been factory pre-set to values recommended by leading carbide tool manufacturers. These tightening values relate specifically to the size of the TORX®, TORX PLUS® or hexagon socket screw. Torque indicators ensure safe and easy loosening of screw connections. Precision : $\pm 10\%$

Torque-indicators




Suitable for applications requiring a non-adjustable i.e. a tamperproof torque blade assembly.

Torque-indicators




Some screw connections require specific torque values so that they can be tightened or loosened easily. Wera torque-indicators are pre-set to torque values recommended by leading carbide tool manufacturers. Pre-set torque between 0.6 Nm and 5.0 Nm, for TORX®, TORX PLUS® and hexagon socket screws, unlimited loosening torque, two handles, tamper-proof.

Precisely adjusted



Torque blade assembly precisely adjusted to the respective screw size for the TORX®, TORX PLUS® and hexagon socket screw profiles.

For difficult-to-access places




Slim 4 mm hexagon blades to reach screws in difficult-to-access places.

Tamperproof



Non-adjustable and tamperproof.

Excess-load signal



Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Weblink

http://products.wera.de/en/torque_tools_series_torque-indicators_300_hex.html

Wera - 300 Hex
05027911001 - 4013288096432

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

More variants of this product family:

								
		nm	ft. lb.	mm	mm	mm	mm	inch
05027910001	2.0	1.4	1.0	4	3.5	65	105	2 9/16
05027911001	2.5	2.0	1.5	4	3.8	65	105	2 9/16
05027912001	3.0	3.0	2.2	4	3.8	65	105	2 9/16

Weblink

http://products.wera.de/en/torque_tools_series_torque-indicators_300_hex.html

Wera - 300 Hex

05027911001 - 4013288096432

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de