

Date: 19 October 2010

Information Sheet No.: TDS00398

## EVO-STIK TILE A WALL FAST SET GROUT FOR CERAMIC TILES A CEMENT BASED, POWDERED WALL TILE GROUT

Evo-Stik Tile A Wall Fast Set Grout For Ceramic Tiles is a cement-based grouting material, suitable for finishing joints of internal and external ceramic tile installations. When set, Evo-Stik Tile A Wall Fast Set Grout For Ceramic Tiles is completely water-resistant and will not wash out of joints. It is recommended for joints up to about 3 mm wide. Before using this product refer to the relevant Health & Safety Data Sheet.

### Uses

- For ceramics, mosaics and natural stone walls.
- Ideal for interior uses including kitchens, bathrooms and showers.
- Easy to mix with water and sets to leave a professional finish that is resistant to mould growth.

### Product Characteristics

<b>Colour</b>	White										
<b>Form</b>	Powder										
<b>Composition</b>	A blend of cement, polymers and selected fillers.										
<b>Specific Gravity</b>	1.6 approximately										
<b>Product Code</b>	<table><tr><td>478701</td><td>500g x 24</td></tr><tr><td>478718</td><td>1.5kg x 8</td></tr><tr><td>478725</td><td>3kg x 4</td></tr><tr><td>478749</td><td>5kg x 3</td></tr><tr><td>478732</td><td>12.5kg x 1</td></tr></table>	478701	500g x 24	478718	1.5kg x 8	478725	3kg x 4	478749	5kg x 3	478732	12.5kg x 1
478701	500g x 24										
478718	1.5kg x 8										
478725	3kg x 4										
478749	5kg x 3										
478732	12.5kg x 1										
<b>Shelf life/storage</b>	6 months from date of manufacture in sealed bags. Store in dry conditions between 5°C and 25°C.										

### Typical Performance Data (approx.)

<b>Flash Point</b>	Inert powders – not relevant
<b>Working life</b>	1 hour approximately.
<b>Application Temps</b>	+5°C and +25°C
<b>UN Number</b>	Not designated for transport.

**Coverage** 1kg of powder, when mixed, will grout approximately 5m<sup>2</sup>. Coverage is dependent on the nature of the substrate, the adhesive bed thickness and the type of tile.

### Directions for use

#### IMPORTANT

Before using Evo-Stik Tile A Wall Fast Set Grout For Ceramic Tiles refer to the relevant Health & Safety Data Sheet. Available at [www.bostik.co.uk](http://www.bostik.co.uk) named as the code above.

#### Preparation

1. Allow at least 24 hours from completion of tile fixing to the application of grout (2 hours when using Evo-Stik Tile A Floor Fast Setting Adhesive For All Tiles).

#### Mixing

1. Wear suitable protective clothing. Mix Evo-Stik Tile A Wall Fast Set Grout For Ceramic Tiles to a thick creamy consistency with clean water.
2. Mix approximately 3 parts powder to 1 part cold water by volume. Pour the water into a clean mixing bucket and gradually add the powder in portions, mixing throughout.
3. Allow this mix to stand for 10 minutes, then re-stir thoroughly; do not add more water. The grout is now ready for use and should remain workable for up to 1 hour. Any mix remaining unused after 1 hour should be discarded.

#### Application

1. Preferably wear protective gloves as wet cement based products can be irritating.
2. Ensure joints are sound, clean, dust free and dry. Follow adhesive manufacturers recommendations

Date: 19 October 2010

Information Sheet No.: TDS00398

regarding drying times. If regrouting existing tiles, remove old grout and clean tiles before use.

- Working in areas of 0.5m<sup>2</sup>, apply the grout to the joints and compact using a squeegee or grout float.
- Using diagonal movements across the tiles, smooth the grout lines and remove any excess grout off the tile surface.
- Immediately after grouting, use a very slightly damp sponge to wipe diagonally across the tiles without disturbing the grouted joints, cleaning the sponge regularly.
- Using a rubber squeegee, sponge or grouting trowel, work the grout thoroughly into the dry tile joints and around all edges. Then with the aid of a pointed wooden tool, the shape and size of a pencil, compact the grout firmly into the joints.
- The process of double grouting whereby the grout is applied in two stages (24 hours apart) is recommended where greater impermeability of the joint is required e.g. showers, swimming pools etc.
- Protect the finished work from water immersion, wet weather and from frost until the grout has cured thoroughly, particularly in cold weather. For example, swimming pools should be left dry for at least 21 days

and shower areas for 14 days before subjecting them to normal service, so that adhesive and grout can mature adequately.

### Cleaning

- Immediately after use, clean tools with warm water.

### Precautions in Use

Do not use at temperatures below 5°C. Not intended for joints in floor tiles, except in small area domestic showers. If joints are greater than 3mm always carry out a test; double grouting may be necessary.

When grouting externally, provide protection from all extremes of climate during and after grouting until the grout is completely hard. If using natural stone tiles, please refer to manufacturer's instructions for protecting and sealing the tiles before and after grouting. Minor colour variation can occur between batches. To ensure colour consistency, use product from the same batch number. Evo-Stik Tile A Wall Fast Set Grout For Ceramic Tiles is not intended for grouting floors.

For Health and Safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for Evo-Stik Tile A Wall Fast Set Grout For Ceramic Tiles.

Date: 19 October 2010

Information Sheet No.: TDS00398

---

Sales & Technical contacts at Bostik	Telephone	Facsimile	Email addresses
Sales	0844 371 1192	01785 241818	<a href="mailto:customer.service@bostik.com">customer.service@bostik.com</a>
Technical advice	0844 371 1197	01785 272867	<a href="mailto:technical.service@bostik.com">technical.service@bostik.com</a>
Technical Data & COSHH (MSDS) sheets	01785 272625	01785 212962	<a href="mailto:stafford.gatehouse@bostik.com">stafford.gatehouse@bostik.com</a>

---

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.