

# Printers and Barcode Scanners

Increase productivity of your test process with our range of tough, portable label printers and barcode scanners. Download test results and asset information directly from the tester and print labels in seconds, for improved traceability.

## Test n Tag Elite 2

**An extremely rugged battery powered mobile printer which prints durable synthetic asset labels.**

Long battery life and high impact resistance make it ideal for use in the field, whatever the environment.

It has a high speed processor and large memory for quick and efficient processing of complex labels, graphics and fonts using Bluetooth wireless technology.



### Key Features

- Rugged Design
- Portable
- Long battery life
- Bluetooth connectivity
- Small 52 x 25mm labels available – ideal for small areas such as plug tops
- Compatible with Rigel Medical testers

### Supplied With

- Battery charger
- Battery pack
- Belt clip
- Label roll

### Compatibility

- Apollo 600
- Apollo 500
- Apollo 400 (with 52 x 25mm labels only)
- PrimeTest 350 (with 52 x 74mm labels only) (firmware update required)
- Rigel 288+ (with 52 x 74mm labels only) (firmware update required)
- Rigel UNI-SIM (with 52 x 74mm labels only) (firmware update required)

**Dimensions:** (W x H x D) 120 x 150 x 62mm

**Weight:** 631g (including battery)

### Part numbers:

339A989 (supplied with 52 x 74mm labels)  
339A995 (supplied with 52 x 25mm labels)

### Labels

- Label roll  
(approx. 130 off 52 x 74mm labels)  
**Part number:** 339A946
- Label roll. Only compatible with Apollo series testers (approx. 350 off 52 x 25mm labels)  
**Part number:** 339A947
- Paper roll x 5 (for results printing)  
**Part number:** 339A949

**IMPORTANT INFORMATION:** Please be aware that use of non-Seaward approved labels can prematurely wear the print heads and so will void your Seaward printer warranty.

[www.seaward.co.uk](http://www.seaward.co.uk)

**Tel:** +44 (0) 191 587 8741  
**Email:** [sales@seaward.co.uk](mailto:sales@seaward.co.uk)

# Test n Tag Pro

## An extremely lightweight and portable battery powered mobile printer.

The Test n Tag Pro prints durable synthetic asset labels which can include barcode, asset number, test date, next test date, user name and test status (dependent on which tester is being used).

It can be used with a rechargeable battery pack or primary cells and is ideal for use with the Apollo series testers via Bluetooth, PrimeTest 250+ via serial cable, or manual testers via the PATMobile Android app.



### Key Features

- Lightweight and Portable
- Small 52 x 25mm labels available – ideal for small areas such as plug tops
- Cost-effective - low start up cost
- Can be used with rechargeable battery pack or use primary cells
- Compatible with Rigel Medical testers

### Supplied With

- Universal charger
- Battery pack
- Primary cell adapter
- Belt clip
- Serial connection cable (serial version only)
- Label roll

### Compatibility

#### Bluetooth Connection

- Apollo 600
- Apollo 500
- Apollo 400 (with 52 x 25mm labels only)
- PrimeTest 100 - via PATMobile app (Android only) (with 52 x 25mm labels only)
- PrimeTest 50 - via PATMobile app (Android only) (with 52 x 25mm labels only)
- Rigel 288+ (results only with paper roll, available separately)
- Rigel UNI-SiM (results only with paper roll, available separately)

#### Serial Connection

- PrimeTest 250+ (only with 52 x 25mm labels)

**Dimensions:** (W x H x D) 95 x 65 x 128mm

### Weight:

446g (including battery & full roll of paper)

### Part numbers:

Serial and Bluetooth Connection  
(supplied with 52 x 74mm labels) 339A980

Serial and Bluetooth Connection  
(supplied with 52 x 25mm labels) 339A987

Serial only connection  
(supplied with 52 x 25mm labels) 339A933

### Labels

- Label roll (approx. 160 off 52 x 74mm labels) **Part number:** 339A944
- Label roll (approx. 400 off 52 x 25mm labels) **Part number:** 339A945
- Paper roll x 5 (for results printing) (only compatible with Apollo Series and Rigel testers)  
**Part number:** 339A949

# Desk Test n Tag

**A desktop thermal transfer printer for long-lasting labels, available in different colours and sizes to suit your application.**

The printer automatically produces test tags that display test results, equipment identification, date of test, barcode ID and can be easily customised to add your own company logo, address and website.

The automatic tag system produces synthetic, durable tags that are printed immediately after test. To give you complete flexibility, duplicate tags can also be printed for attachment to contracts etc.



## Key Features

- High-quality, durable and tamper-proof labels
- Labels available in a variety of sizes and colours
- Customisable test labels - add your own pass and fail designs
- Cost-effective label printing

## Supplied with

- Power supply
- Connection cables
- Configuration disc
- White label roll
- Black ink ribbon

## Compatibility

Serial connection:

- Supernova Elite
- Europa Plus
- HAL Series
- SafeCheck 8
- STM/L

**Dimensions:** (W x H x D) 213 x 188 x 314mm

## Weight:

2.8kg

## Part numbers:

- 312A916 (supplied with 100 x 50mm labels)\*
- 312A973 (supplied with 35 x 45mm labels)\*

\*Please Note: Printers come configured to use the label size they are supplied with. This can be changed by the user at any point if required.

## Labels

- Yellow (approx. 1000 off 100 x 50mm)  
**Part number:** 312A956
- Blue (approx. 1000 off 100 x 50mm)  
**Part number:** 312A957
- Red (approx. 1000 off 100 x 50mm)  
**Part number:** 312A961
- Green (approx. 1000 off 100 x 50mm)  
**Part number:** 312A962
- White (approx. 1000 off 100 x 50mm)  
**Part number:** 312A951
- White (approx. 1000 off 35 x 45mm)  
**Part number:** 312A972
- Black ink ribbon  
**Part number:** 312A952

# Bluetooth Barcode Scanner

**A portable asset label ID laser scanner with Bluetooth interface.**

It is extremely compact and lightweight, making it ideal for mobile applications. USB rechargeable lithium-ion battery. Reads 1D barcode formats code 39, code 93 & code 128.



## Key Features

- Lightweight & portable
- Wireless Bluetooth connectivity
- Compatible with Apollo series of testers
- Compatible with Rigel Medical testers

## Compatibility

- Apollo 600
- Apollo 500
- Apollo 400
- PrimeTest 350
- PrimeTest 300
- Rigel 288+
- Rigel UNI-SiM

**Dimensions:** (W x H x D) 30 x 60 x 14mm

**Weight:** 30g

**Part number:** 339A923

# CCD Barcode Scanner

**A non contact barcode label scanner for rapid, error free entry of appliance number, test code and asset details.**

Connects to Supernova Elite via serial connection. Reads 1D barcode formats code 39 & code 128.



## Key Features

- Connects directly to the tester via serial cable
- Hand-held and easy to use
- Compatible with Supernova Elite and Europa Plus testers

## Compatibility

- Supernova Elite
- Europa Plus
- HAL Series
- STM/L
- SafeCheck 8

**Dimensions:** (W x H x D) 164 x 77.5 x 63mm

**Weight:** 160g (excluding lead)

**Part number:** 194A922

Printer and scanner compatibility	Seaward Part Number	Apollo 600	Apollo 500	Apollo 400	Supernova Elite	PrimeTest 250+	PrimeTest 100	PrimeTest 50	HAL Series	SafeCheck 8	STM/L	Rigel 288+	Rigel UNI-SiM
Test n Tag Elite 2 printer with large or small labels	Supplied with 52 x 74mm labels 339A989	✓	✓									✓	✓
	Supplied with 52 x 25mm labels 339A995	✓	✓	✓									
Test n Tag Pro printer with large or small labels	Serial only printer supplied with 52 x 25mm labels 339A933					✓							
	Bluetooth/Serial printer supplied with 52 x 74mm labels 339A980	✓	✓									✓†	✓†
	Bluetooth/Serial printer supplied with 52 x 25mm labels 339A987	✓	✓	✓		✓ (via serial lead)	✓ (via PATMobile app*)	✓ (via PATMobile app*)				✓†	✓†
Desk Test n Tag printer with large or small labels	Supplied with 100 x 50mm labels 312A916				✓				✓	✓	✓		
	Supplied with 35 x 45mm labels 312A973				✓				✓	✓	✓		
Bluetooth barcode scanner	339A923	✓	✓	✓								✓	✓
CCD barcode scanner	194A922				✓				✓	✓	✓		

\*Android only †With results only paper roll. Results only paper roll can be used with Test n Tag Pro Serial/Bluetooth and Test n Tag Elite models - must be purchased separately.

Printer label compatibility	Part number	Test n Tag Elite 2	Test n Tag Pro	Desk Test n Tag
Label roll without perforation (approx. 160 off 52 x 74mm labels)	339A944		✓	
Label roll (approx. 400 off 52 x 25mm labels)	339A945		✓	
Label roll (approx. 130 off 52 x 74mm labels)	339A946	✓	✓	
Label roll (approx. 350 off 52 x 25mm labels)	339A947	✓ (only compatible with Apollo Series testers)	✓	
Yellow (approx. 1000 off 100 x 50mm labels)	312A956			✓
Blue (approx. 1000 off 100 x 50mm labels)	312A957			✓
Red (approx. 1000 off 100 x 50mm labels)	312A961			✓
Green (approx. 1000 off 100 x 50mm labels)	312A962			✓
White (approx. 1000 off 100 x 50mm labels)	312A951			✓
White (approx. 1000 off 35 x 45mm)	312A972			✓
Black Ink Ribbon	312A952			✓
Paper roll x 5 (for results printing)	339A949	✓	✓	