

101 Soft-faced hammer with nylon head sections, # 7 x 60 mm

Series Soft-Faced Hammers



EAN/GTIN:	4013288001412	Dimension:	380x125x60 mm
Part no.:	05000335001	Weight:	1140 g
Article no.:	101	Country of origin:	CZ
		Customs tariff number:	82052000

- Powerful hammering with surface protection
- Soft-face hammers with hammer head out of nylon
- Suitable for sheet metal and renovation work as well as for tent, hall and fair booth construction jobs
- Inseparable and secure connection between the hammer handle and head
- High-quality ashwood handle

Wera soft-face hammers. Double-sided conical design for a secure, inseparable connection between the hammer handle and head. The hammer head is made out of nylon; the handle out of high quality ash wood. Diverse applications thanks to the interchangeable soft-face hammer heads. Suitable for sheet metal and renovation work as well as for tent, hall and fair booth construction jobs.

Weblink

http://products.wera.de/en/series_soft-faced_hammers_101.html

Wera - 101
05000335001 - 4013288001412

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series Soft-Faced Hammers

Soft-faced hammers



Powerful hammering with surface protection.

Wide range of applications



They come in soft, medium and hard designs for a wide range of applications from universal use to splinter-free applications on sharp-edged work pieces.

High quality ash wood



Powerful work is ensured with handles out of high quality ash wood.

Colour guidance system



Colour guidance system • Yellow = Repair/maintenance work with high demands • Red = Suitable for hammering sharp-edged work pieces; bodyshops, automotive, engineering • White = Suitable for metal processing and removal of dents; tent, large building and exhibition stand construction

Secure



The double-sided conical design creates an unbreakable and secure link between the handle and head of the hammer.

Versatile



Versatile use thanks to the soft faced heads that can be retrospectively fitted.

Weblink

http://products.wera.de/en/series_soft-faced_hammers_101.html

Wera - 101
05000335001 - 4013288001412

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

101 Soft-faced hammer with nylon head sections, # 7 x 60 mm

Series Soft-Faced Hammers



More variants of this product family:



mm

mm

05000305001	1	22	75	250.0
05000310001	2	27	90	265.0
05000315001	3	32	95	280.0
05000320001	4	35	105	290.0
05000325001	5	40	110	320.0
05000330001	6	50	115	340.0
05000335001	7	60	135	380.0

Weblink

http://products.wera.de/en/series_soft-faced_hammers_101.html

Wera - 101

05000335001 - 4013288001412

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de