

## 102 Soft-faced hammer with urethane head sections, # 5 x 40 mm

### Series Soft-Faced Hammers



<b>EAN/GTIN:</b>	4013288001535	<b>Dimension:</b>	320x110x40 mm
<b>Part no.:</b>	05000525001	<b>Weight:</b>	567 g
<b>Article no.:</b>	102	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82052000

- Powerful hammering with surface protection
- Soft-face hammers with hammer head out of urethane; semi-hard
- For hammering sharp-edged workpieces; car body, engineering and automotive applications.
- Inseparable and secure connection between the hammer handle and head
- High-quality ashwood handle

Wera soft-face hammers. Double-sided conical design for a secure, inseparable connection between the hammer handle and head. The hammer head is made out of semi-hard urethane; the handle out of high quality ash wood. Diverse applications thanks to the interchangeable soft-face hammer heads. Suitable for car body, engineering and automotive applications.

#### Weblink

[http://products.wera.de/en/series\\_soft-faced\\_hammers\\_102.html](http://products.wera.de/en/series_soft-faced_hammers_102.html)

Wera - 102

05000525001 - 4013288001535

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

Series Soft-Faced Hammers

Soft-faced hammers



Powerful hammering with surface protection.

Wide range of applications



They come in soft, medium and hard designs for a wide range of applications from universal use to splinter-free applications on sharp-edged work pieces.

High quality ash wood



Powerful work is ensured with handles out of high quality ash wood.

Colour guidance system



Colour guidance system • Yellow = Repair/maintenance work with high demands • Red = Suitable for hammering sharp-edged work pieces; bodyshops, automotive, engineering • White = Suitable for metal processing and removal of dents; tent, large building and exhibition stand construction

Secure



The double-sided conical design creates an unbreakable and secure link between the handle and head of the hammer.

Versatile



Versatile use thanks to the soft faced heads that can be retrospectively fitted.

Weblink

[http://products.wera.de/en/series\\_soft-faced\\_hammers\\_102.html](http://products.wera.de/en/series_soft-faced_hammers_102.html)

Wera - 102

05000525001 - 4013288001535

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

# 102 Soft-faced hammer with urethane head sections, # 5 x 40 mm

## Series Soft-Faced Hammers



More variants of this product family:



mm

mm

05000505001	1	22	75	250.0
05000510001	2	27	90	265.0
05000515001	3	32	95	280.0
05000520001	4	35	105	290.0
<b>05000525001</b>	<b>5</b>	<b>40</b>	<b>110</b>	<b>320.0</b>
05000530001	6	50	115	340.0
05000535001	7	60	135	380.0

### Weblink

[http://products.wera.de/en/series\\_soft-faced\\_hammers\\_102.html](http://products.wera.de/en/series_soft-faced_hammers_102.html)

Wera - 102

05000525001 - 4013288001535

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)