

# DataTraveler 50

kingston.com/usb

## Compact, capless storage in a metal case.

DataTraveler® 50 is a lightweight USB Flash drive that's available in capacities from 8GB to 128GB<sup>1</sup>. The drive's compact, capless design features a metal casing that complements any compatible device and colourful accents that range by drive capacity. Fast<sup>2</sup> USB 3.1 Gen 1 (USB 3.0)<sup>3</sup> performance ensures data transfer of music, video and more is quick and easy. Backward compatible with existing USB 2.0 ports for convenience, the drive is also customisable with your logo and/or digital files.<sup>4</sup> DT 50 is backed by a five-year warranty, free technical support and legendary Kingston® reliability.

- › Compact, lightweight, capless design
- › Metal casing with colourful accent by capacity
- › Fast<sup>2</sup> USB 3.1 Gen 1 (USB 3.0)<sup>3</sup> performance
- › Customisable with your logo and/or digital files<sup>4</sup>



Features/specs on reverse >>

# DataTraveler 50

## FEATURES/BENEFITS

- > **Small and compact** — The lightweight storage solution that's easy to take with you.
- > **Metal casing** — Complements any compatible device; no cap to lose or break.
- > **USB 3.1 Gen 1 (USB 3.0)<sup>3</sup> speeds<sup>2</sup>** — Faster than USB 2.0 Flash drives.
- > **Large capacities<sup>1</sup>** — Up to 128GB to take all your files with you.

## SPECIFICATIONS

- > **Capacities<sup>1</sup>** 8GB, 16GB, 32GB, 64GB, 128GB
- > **Speed<sup>2</sup>** USB 3.1 Gen 1<sup>3</sup>
  - 8GB–16GB — 30MB/s read, 5MB/s write
  - 32GB–128GB — 110MB/s read, 15MB/s write
- > **Dimensions** 44.9mm x 20mm x 9.2mm
- > **Operating Temperature** 0°C to 60°C
- > **Storage Temperature** -20°C to 85°C
- > **Warranty/support** 5-year warranty with free technical support



## COMPATIBILITY TABLE

	USB 3.0/3.1 <sup>3</sup>	USB 2.0
Windows® 10	✓	✓
Windows 8.1	✓	✓
Windows 8	✓	✓
Windows 7 (SP1)	✓	✓
Windows Vista (SP2)	✓	✓
Mac OS X v.10.8 +	✓	✓
Linux (v. 2.6.x +)	✓	✓
Chrome	✓	✓

## PART NUMBERS

DT50/8GB  
DT50/16GB  
DT50/32GB  
DT50/64GB  
DT50/128GB

<sup>1</sup> Some of the listed capacity on a Flash storage device is used for formatting and other functions and is thus not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at [kingston.com/flashguide](http://kingston.com/flashguide).

<sup>2</sup> Speed may vary due to host hardware, software and usage.

<sup>3</sup> USB 3.1 Gen 1 performance requires a host device with a USB 3.0 or 3.1 port.

<sup>4</sup> Conditions apply; contact your local sales representative.

