

Product information

00 21 30

Tool Case "Focus" Electric



Roomy and variable: the power tool case with large base tray and tool range

- Equipped with 23 brand tools, partly VDE tested according to DIN EN/ IEC 60900
- 90 mm deep base tray with variable compartments (e.g. for measuring and testing instruments)
- Max. payload: 25 kg
- Volume: 35 litres
- Sturdy ABS hard-shell construction with aluminium frame and wraparound buffer protection
- Document compartment and pen holding straps
- One removable tool plate, with elastic loops on both sides
- One cover plate with elastic loops and tool protection cloth
- Sturdy metal locks and three-digit combination lock protect the contents of the case
- Strong, ergonomic handle
- Feet on both sides
- Colour: silver, aluminium look
- External dimensions (W x H x D): 520 x 420 x 210 mm; internal dimensions (W x H x D): 480 x 360 x 200 mm






General


















Article No.	00 21 30
EAN	4003773051084
weight	8,745 g
Dimensions	510 x 213 x 421 mm
Reach	yes
RohS	no

Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112117

Content

00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems
03 06 180	1 x Combination Pliers 
12 40 200	1 x Self-Adjusting Insulation Stripper (0,03 – 10,0 mm ²) 
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool (Ø 8,0 – 13,0 mm) 
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) 
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) 
70 06 125	1 x Diagonal Cutter

Content	
	
70 06 160	1 x Diagonal Cutter 
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool 
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool 
87 03 250	1 x KNIPEX Cobra® Hightech Water Pump Pliers 
92 27 62	1 x Precision Tweezers insulated 
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) 
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm) 
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (4,0 mm) 
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) 
98 20 65 SL	1 x Screwdriver (Slim) for slotted screws (6,5 mm) 
98 20 80	1 x Screwdrivers for slotted screws (8,0 mm) 
98 24 00	1 x Screwdriver for cross recessed screws Phillips® (PH0) 
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) 
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2) 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) 
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2) 
98 56	1 x Cable Knife with replaceable blade

technical change and errors excepted