

**EXTERIOR WOOD PROTECTOR LIBERON - 1597**

**SAFETY DATA SHEET**

(REACH regulation (EC) n° 1907/2006 - n° 453/2010)

**SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING**

**1.1. Product identifier**

Product name : EXTERIOR WOOD PROTECTOR LIBERON

Product code : 1597.

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

Woodcare product

**1.3. Details of the supplier of the safety data sheet**

Registered company name : LIBERON Ltd.

Address : Mountfield Industrial Estate.NEW ROMNEY.KENT TN28 8XU.ENGLAND.

Telephone : (+44) 1797 36 75 55. Fax : (+44) 1797 36 75 75.

fds.produits@v33.com

www.liberon.co.uk

**1.4. Emergency telephone number : .**

Association/Organisation : .

**Other emergency numbers**

UK - National Poisons Information Service

**SECTION 2 : HAZARDS IDENTIFICATION**

**2.1. Classification of the substance or mixture**

**In compliance with EC regulation No. 1272/2008 and its amendments.**

May produce an allergic reaction (EUH208).

This mixture does not present a physical hazard. Refer to the recommendations regarding the other products present on the site.

This mixture does not present a health hazard with the exception of possible occupational exposure thresholds (see paragraphs 3 and 8).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

**In compliance with directives 67/548/EEC, 1999/45/EC and their amendments.**

May produce an allergic reaction.

This mixture does not present a physical hazard. Refer to the recommendations regarding the other products present on the site.

This mixture does not present a health hazard with the exception of possible occupational exposure thresholds (see paragraphs 3 and 8).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

**2.2. Label elements**

**In compliance with EC regulation No. 1272/2008 and its amendments.**

Additional labeling :

EUH208 Contains HYDROXYPHENYL BENZOTRIAZOL. May produce an allergic reaction.

EUH208 Contains 1,2-BENZISOTHIAZOL-3(2H)-ONE. May produce an allergic reaction.

Precautionary statements - General :

P102 Keep out of reach of children.

Precautionary statements - Prevention :

P271 Use only outdoors or in a well-ventilated area.

Precautionary statements - Disposal :

P501 Dispose of contents/container to a waste collection center (contact the local authority)

**2.3. Other hazards**

The mixture does not contain any substances classified as 'Substances of Very High Concern' (SVHC) by the European Chemical Agency (ECHA) under article 57 of REACH: <http://echa.europa.eu/fr/candidate-list-table>

The mixture satisfies neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

**EXTERIOR WOOD PROTECTOR LIBERON - 1597****SECTION 3 : COMPOSITION/INFORMATION ON INGREDIENTS****3.1. Substances**

No substances fulfil the criteria set forth in annexe II section A of the REACH regulation (EC) n° 1907/2006.

**3.2. Mixtures****Composition :**

Identification	(EC) 1272/2008	67/548/EEC	Note	%
INDEX: 603-064-00-3 CAS: 107-98-2 EC: 203-539-1 REACH: 01-2119457435-35  MONOPROPYLENE GLYCOL METHYL ETHER	GHS02, GHS07 Wng Flam. Liq. 3, H226 STOT SE 3, H336	R10 R67	[1]	0 <= x % < 2.5
INDEX: 607-176-00-3 EC: 400-830-7  HYDROXYPHENYL BENZOTRIAZOL	GHS07, GHS09 Wng Skin Sens. 1, H317 Aquatic Chronic 2, H411	Xi,N Xi;R43 N;R51/53		0 <= x % < 2.5
INDEX: 613_088_00_6 CAS: 2634-33-5 EC: 220-120-9  1,2-BENZISOTHIAZOL-3(2H)-ONE	GHS07, GHS05, GHS09 Dgr Acute Tox. 4, H302 Skin Irrit. 2, H315 Skin Sens. 1B, H317 Eye Dam. 1, H318 Aquatic Acute 1, H400 M Acute = 1	Xn,N Xn;R22 Xi;R38-R41-R43 N;R50		0 <= x % < 2.5

**Information on ingredients :**

[1] Substance for which maximum workplace exposure limits are available.

**SECTION 4 : FIRST AID MEASURES**

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

**4.1. Description of first aid measures****In the event of exposure by inhalation :**

In the event of an allergic reaction, seek medical attention.

**In the event of splashes or contact with eyes :**

Wash thoroughly with soft, clean water for 15 minutes holding the eyelids open.

**In the event of splashes or contact with skin :**

In the event of an allergic reaction, seek medical attention.

**In the event of swallowing :**

In the event of swallowing, if the quantity is small (no more than one mouthful), rinse the mouth with water and consult a doctor.

Keep the person exposed at rest. Do not force vomiting.

Seek medical attention, showing the label.

If swallowed accidentally, call a doctor to ascertain whether observation and hospital care will be necessary. Show the label.

**4.2. Most important symptoms and effects, both acute and delayed**

No data available.

**4.3. Indication of any immediate medical attention and special treatment needed**

No data available.

**SECTION 5 : FIREFIGHTING MEASURES**

Non-flammable.

**5.1. Extinguishing media****Suitable methods of extinction**

In the event of a fire, use :

- sprayed water or water mist
- foam
- multipurpose ABC powder
- BC powder

**EXTERIOR WOOD PROTECTOR LIBERON - 1597**

---

- carbon dioxide (CO<sub>2</sub>)

**Unsuitable methods of extinction**

In the event of a fire, do not use :

- water jet

**5.2. Special hazards arising from the substance or mixture**

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)

- carbon dioxide (CO<sub>2</sub>)

**5.3. Advice for firefighters**

No data available.

---

**SECTION 6 : ACCIDENTAL RELEASE MEASURES**

**6.1. Personal precautions, protective equipment and emergency procedures**

Consult the safety measures listed under headings 7 and 8.

**For fire-fighters**

Fire-fighters will be equipped with suitable personal protective equipment (See section 8).

**6.2. Environmental precautions**

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

**6.3. Methods and material for containment and cleaning up**

Clean preferably with a detergent, do not use solvents.

**6.4. Reference to other sections**

No data available.

---

**SECTION 7 : HANDLING AND STORAGE**

Requirements relating to storage premises apply to all facilities where the mixture is handled.

**7.1. Precautions for safe handling**

Always wash hands after handling.

Ensure that there is adequate ventilation, especially in confined areas.

**Fire prevention :**

Handle in well-ventilated areas.

Prevent access by unauthorised personnel.

**Recommended equipment and procedures :**

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Packages which have been opened must be reclosed carefully and stored in an upright position.

**Prohibited equipment and procedures :**

No smoking, eating or drinking in areas where the mixture is used.

**7.2. Conditions for safe storage, including any incompatibilities**

Do not allow to freeze

**Storage**

Keep out of reach of children.

Keep the container tightly closed in a dry, well-ventilated place.

The floor must be impermeable and form a collecting basin so that, in the event of an accidental spillage, the liquid cannot spread beyond this area.

**Packaging**

Always keep in packaging made of an identical material to the original.

**7.3. Specific end use(s)**

No data available.

**EXTERIOR WOOD PROTECTOR LIBERON - 1597****SECTION 8 : EXPOSURE CONTROLS/PERSONAL PROTECTION****8.1. Control parameters****Occupational exposure limits :**

- European Union (2009/161/EU, 2006/15/EC, 2000/39/EC, 98/24/EC)

CAS	VME-mg/m <sup>3</sup>	VME-ppm	VLE-mg/m <sup>3</sup>	VLE-ppm	Notes
107-98-2	375	100	568	150	Peau

- ACGIH TLV (American Conference of Governmental Industrial Hygienists, Threshold Limit Values, 2010) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
107-98-2	100 ppm	150 ppm	-	-	-

- Germany - AGW (BAuA - TRGS 900, 21/06/2010) :

CAS	VME :	VME :	Excess	Notes
107-98-2	100 ml/m <sup>3</sup>	370 mg/m <sup>3</sup>	2(I)	DFG, Y

- France (INRS - ED984 :2008) :

CAS	VME-ppm :	VME-mg/m <sup>3</sup>	VLE-ppm :	VLE-mg/m <sup>3</sup>	Notes :	TMP No :
107-98-2	50	188	100	375	*	84

- UK / WEL (Workplace exposure limits, EH40/2005, 2007) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
107-98-2	100 ppm	150 ppm	-	-	-

**8.2. Exposure controls****Personal protection measures, such as personal protective equipment**

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

**- Eye / face protection**

Avoid contact with eyes.

Use eye protectors designed to protect against liquid splashes

Before handling, wear safety goggles in accordance with standard EN166.

**- Hand protection**

Wear suitable protective gloves in the event of prolonged or repeated skin contact.

Type of gloves recommended :

- Natural latex
- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR))
- PVC (polyvinyl chloride)
- Butyl Rubber (Isobutylene-isoprene copolymer)

**- Body protection**

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

**SECTION 9 : PHYSICAL AND CHEMICAL PROPERTIES****9.1. Information on basic physical and chemical properties****General information :**

Physical state : Viscous liquid.

**Important health, safety and environmental information**

pH : 8.50 .  
Slightly basic.

Boiling point/boiling range : Not relevant.

Flash point interval : Not relevant.

Vapour pressure (50°C) : Not relevant.

Density : 0.9-1.1

Water solubility : Dilutable.

Melting point/melting range : Not relevant.

Self-ignition temperature : Not relevant.

Decomposition point/decomposition range : Not relevant.

**EXTERIOR WOOD PROTECTOR LIBERON - 1597**

---

**9.2. Other information**

No data available.

---

**SECTION 10 : STABILITY AND REACTIVITY**

**10.1. Reactivity**

No data available.

**10.2. Chemical stability**

This mixture is stable under the recommended handling and storage conditions in section 7.

**10.3. Possibility of hazardous reactions**

When exposed to high temperatures, the mixture can release hazardous decomposition products, such as carbon monoxide and dioxide, fumes and nitrogen oxide.

**10.4. Conditions to avoid**

Avoid :

- frost

**10.5. Incompatible materials**

**10.6. Hazardous decomposition products**

The thermal decomposition may release/form :

- carbon monoxide (CO)

- carbon dioxide (CO<sub>2</sub>)

---

**SECTION 11 : TOXICOLOGICAL INFORMATION**

**11.1. Information on toxicological effects**

Splashes in the eyes may cause irritation and reversible damage

**11.1.2. Mixture**

**Respiratory or skin sensitisation :**

Contains at least one sensitising substance. May cause an allergic reaction.

---

**SECTION 12 : ECOLOGICAL INFORMATION**

**12.1. Toxicity**

**12.1.2. Mixtures**

No aquatic toxicity data available for the mixture.

**12.2. Persistence and degradability**

No data available.

**12.3. Bioaccumulative potential**

No data available.

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

No data available.

**12.6. Other adverse effects**

No data available.

---

**SECTION 13 : DISPOSAL CONSIDERATIONS**

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

CAUTION: Oil cloths can self combust. Do not leave impregnated cloths in bundles. Before discarding lay them flat outside to dry to avoid a fire hazard.

**13.1. Waste treatment methods**

Do not pour into drains or waterways.

**Waste :**

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

**EXTERIOR WOOD PROTECTOR LIBERON - 1597**

---

**Soiled packaging :**

Empty container completely. Keep label(s) on container.  
Give to a certified disposal contractor.

---

**SECTION 14 : TRANSPORT INFORMATION**

Exempt from transport classification and labelling.

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2013 - IMDG 2012 - ICAO/IATA 2013).

---

**SECTION 15 : REGULATORY INFORMATION**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**- Classification and labelling information included in section 2:**

The following regulations have been used:

- Directive 67/548/EEC and its adaptations
- Directive 1999/45/EC and its adaptations
- Regulation EC 1272/2008 modified by regulation EC 618/2012

**- Container information:**

No data available.

**- Particular provisions :**

No data available.

**15.2. Chemical safety assessment**

No data available.

---

**SECTION 16 : OTHER INFORMATION**

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

**In compliance with directives 67/548/EEC, 1999/45/EC and their amendments.**

Contains :

Contains 607-176-00-3 HYDROXYPHENYL BENZOTRIAZOL. May produce an allergic reaction.

Safety phrase :

- |      |                                    |
|------|------------------------------------|
| S 2  | Keep out of the reach of children. |
| S 29 | Do not empty into drains.          |
| S 51 | Use only in well-ventilated areas. |

**Title for H, EUH and R indications mentioned in section 3 :**

- |         |   |
|---------|---|
| H226    | Flammable liquid and vapour.  |
| H302    | Harmful if swallowed.   |
| H315    | Causes skin irritation.   |
| H317    | May cause an allergic skin reaction.  |
| H318    | Causes serious eye damage.  |
| H336    | May cause drowsiness or dizziness.  |
| H400    | Very toxic to aquatic life.   |
| H411    | Toxic to aquatic life with long lasting effects.  |
| R 10    | Flammable.  |
| R 22    | Harmful if swallowed.   |
| R 38    | Irritating to skin.   |
| R 41    | Risk of serious damage to eyes.   |
| R 43    | May cause sensitisation by skin contact.  |
| R 50    | Very toxic to aquatic organisms.  |
| R 51/53 | Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |
| R 67    | Vapours may cause drowsiness and dizziness.   |

---

**EXTERIOR WOOD PROTECTOR LIBERON - 1597**

---

**Abbreviations :**

ADR : European agreement concerning the international carriage of dangerous goods by Road.

IMDG : International Maritime Dangerous Goods.

IATA : International Air Transport Association.

ICAO : International Civil Aviation Organisation

RID : Regulations concerning the International carriage of Dangerous goods by rail.

WGK : Wassergefährdungsklasse (Water Hazard Class).