



Triple-deck terminal block; 6-conductor ground terminal block; PE; with marker carrier; green-yellow housing; internal commoning; suitable for Ex e II applications

Item No.: 2002-3237



Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2002-3237
GTIN / EAN	4044918989718
Content	1

Notes

Technical data

Miscellaneous



Ratings per	IEC/EN 60947-7-2
Type of wiring	Front-entry wiring
Total number of connection points	6
Total number of potentials	1


Printview: Triple-deck terminal block; 6-conductor ground terminal block; PE; with marker carrier; green-yellow housing; internal commoning; suitable for Ex e II applications - Item No.: 2002-3237

Technical data	
<i>Number of levels</i>	3
<i>Connection technology</i>	Push-in CAGE CLAMP®
<i>Actuation type</i>	Push-in
<i>Connectable conductor materials</i>	Copper
<i>Nominal cross section</i>	2.5 mm ²
<i>Solid conductor</i>	0.25 ... 4 mm ² / 22 ... 12 AWG
<i>Solid conductor, push-in termination</i>	0.75 ... 4 mm ² / 18 ... 12 AWG
<i>Fine-stranded conductor</i>	0.25 ... 4 mm ² / 22 ... 12 AWG
<i>Fine-stranded conductor with ferrule, push-in termination, f</i>	0.75 mm ² / 18 AWG
<i>Strip length</i>	10 ... 12 mm / 0.39 ... 0.47 Inch
<i>Width</i>	5.2 mm / 0.205 Inch
<i>Height from upper-edge of DIN-35 rail</i>	81.3 mm / 3.201 Inch
<i>Depth</i>	93.3 mm / 3.673 Inch
<i>Design</i>	horizontal
<i>Type of mounting</i>	Carrier rail 35 x 15
<i>Potential marking</i>	PE
<i>Marking level</i>	Center/side marking
<i>Color</i>	green-yellow
<i>Insulating material</i>	Polyamide 66 (PA 66)
<i>Fire load [MJ]</i>	0.334 [MJ]
<i>Weight [g]</i>	21.256 [g]
<i>Product Family</i>	TOPJOB® S
<i>Main product function</i>	Multilevel terminal blocks
<i>Product type</i>	Through rail-mount term. blocks

Images & drawings







Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.