

NETGEAR EX6110 Network repeater White

Brand : NETGEAR
Product name : EX6110
Product code: EX6110-100UKS

Netgear AC1200, WLAN 802.11 b/g/n/ac, FastLane Technology

NETGEAR EX6110 Network repeater White:

NETGEAR AC1200 Dual Band WiFi Range Extender boosts your existing network range, delivering AC dual band WiFi up to 1200Mbps. FastLane technology improves performance using both WiFi bands. High-power amplifiers and internal antenna array increase range for whole home coverage. It works with any standard WiFi router and is ideal for HD video streaming and gaming. Get the connectivity you need for iPads®, smartphones, laptops and more.

Boost the range of your WiFi network to every corner of your home for maximum WiFi performance.

Create faster WiFi access for 802.11 b/g/n & ac WiFi devices.
Extend 2.4 & 5GHz WiFi up to 1200Mbps & reduce interference.
Smart LED indicators find the best location for your range extender.
FastLane™ Technology - Use both WiFi bands to establish one super high-speed connection; ideal for HD streaming & gaming.
Works with any WiFi router



Performance		Network	
Type *	Network repeater	Security algorithms	WEP, WPA, WPA-PSK, WPA2, WPA2-PSK, WPS
Data transfer rate	1200 Mbit/s	Design	
Network		Product colour *	White
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n	Mounting type	Wall
Wi-Fi	✓	LED indicators	Network, Power, Reset
Wi-Fi standards	802.11a, 802.11b, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)	Weight & dimensions	
Wi-Fi data rate (max)	1200 Mbit/s	Width	72.5 mm
Wi-Fi band	Dual-band (2.4 GHz / 5 GHz)	Depth	64.8 mm
Bandwidth	2.4 GHz	Height	72.5 mm
		Weight	152 g



0606449120844



606449120844

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.