

StarTech.com 1m DVI to VGA Display Monitor Cable M/M - DVI to VGA (15 Pin)

Brand : StarTech.com

Product code: DVIVGAMM1M

Product name : 1m DVI to VGA Display Monitor Cable M/M - DVI to VGA (15 Pin)

1m DVI to VGA Display Monitor Cable M/M - DVI to VGA (15 Pin)

StarTech.com 1m DVI to VGA Display Monitor Cable M/M - DVI to VGA (15 Pin):

Connect a VGA display to a PC or Mac® with a DVI Analog Video Card
The DVIVGAMM1M DVI to VGA Display Monitor Cable (1m) features a DVI-A male connector and a VGA male connector, enabling you to connect a VGA display to a PC or Mac® computer with a DVI-I analog output.
Expertly designed and constructed of only high quality materials, the DVI-A to VGA cable is backed by StarTech.com's Lifetime Warranty.
The StarTech.com Advantage

- Cost-effective solution for connecting a VGA Display to a PC or Mac® computer with DVI-I analog output
- Ensures a solid, high quality connection between connected devices, using gold-plated contacts and molded connectors with strain relief
- Delivers dependable performance, backed by lifetime warranty



Features		Weight & dimensions	
Connector contacts plating	Nickel	Weight	119 g
Cable length *	1 m	Packaging data	
Connector 1 *	DVI-A	Package width	200 mm
Connector 2 *	VGA (D-Sub)	Package depth	220 mm
Product colour	Black	Package height	29 mm
Connector gender	Male/Male	Package weight	135 g
Certificates		Logistics data	
Compliance certificates	RoHS	Harmonized System (HS) code	84733080



0065030849166



065030849166



5054533236165



5704174544999

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.