


StarTech.com 24in Internal 5 pin USB IDC Motherboard Header Cable F/F

Brand : StarTech.com

Product code: USBINT5PIN24

Product name : 24in Internal 5 pin USB IDC Motherboard Header Cable F/F



StarTech.com 24in Internal 5 pin USB IDC Motherboard Header Cable F/F

StarTech.com 24in Internal 5 pin USB IDC Motherboard Header Cable F/F:

Connect a front panel USB hub or card reader directly to a motherboard header connector

The USBINT5PIN24 Internal USB Cable features two 5-pin USB motherboard header connectors, enabling you to connect a front panel USB hub or card reader directly to the motherboard header ports. This 24in/2ft cable provides a convenient solution for connecting multi-function front panels, or any device that relies on internal USB ports, directly to a motherboard or expansion card USB IDC (Header) connection, without having to install additional cards or run cables externally to the rear ports. Constructed of high quality materials and expertly constructed for durable performance, the 5-pin USB Header Cable is backed by StarTech.com's Lifetime Warranty.



The StarTech.com Advantage


Features		Weight & dimensions	
Cable length *	0.609 m	Width	130 mm
Connector 1 *	IDC	Depth	609.6 mm
Connector 2 *	IDC	Height	50 mm
Connector 1 gender	Female	Weight	23 g
Connector 2 gender	Female	Packaging data	
Connector 1 form factor	Straight	Package width	125 mm
Connector 2 form factor	Straight	Package depth	225 mm
Product colour	Black	Package height	10 mm
Certificates		Package weight	23 g
Compliance certificates	RoHS	Logistics data	
Certification	CE, REACH	Harmonized System (HS) code	84733080



0065030848459



065030848459



0650308484592



650308484592

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.