

StarTech.com 6 ft Slim 3.5mm Right Angle Stereo Audio Cable - M/M

Brand : StarTech.com

Product code: MU6MMS2RA

Product name : 6 ft Slim 3.5mm Right Angle Stereo Audio Cable - M/M

StarTech.com 6 ft Slim 3.5mm Right Angle Stereo Audio Cable - M/M
StarTech.com 6 ft Slim 3.5mm Right Angle Stereo Audio Cable - M/M. Connector 1: 3.5mm, Connector 1 gender: Male, Connector 2: 3.5mm, Connector 2 gender: Male, Connector contacts plating: Gold, AWG wire size: 30, Cable length: 1.8 m, Product colour: Black

Features		Weight & dimensions	
Cable length *	1.8 m	Cable diameter	2.5 mm
Connector 1 *	3.5mm	Weight	19 g
Connector 1 gender *	Male	Packaging content	
Connector 2 *	3.5mm	Quantity per pack	1 pc(s)
Connector 2 gender *	Male	Packaging data	
Connector 1 form factor	Angled	Package width	128 mm
Connector 2 form factor	Angled	Package depth	220 mm
Connector contacts plating	Gold	Package height	7 mm
Product colour *	Black	Package weight	30 g
Jacket material	Polyvinyl chloride (PVC)	Other features	
AWG wire size	30	Quantity outer carton	400 pc(s)
Certificates		Logistics data	
Compliance certificates	RoHS	Harmonized System (HS) code	85189000





0065030841276



065030841276



0778889089088



778889089088

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.