



APC Power Cord, C20 to IEC309 (16A), 2.5m

Brand : APC
Product code: AP9899
Product name : Power Cord, C20 to IEC309 (16A), 2.5m




Power Cord, C20 to IEC309 (16A), 2.5m

APC Power Cord, C20 to IEC309 (16A), 2.5m:

This cable connects an IEC C19 outlet to an IEC 309-16A connector It can be used as a means to plug in a 16A IEC 309 plug into a Rack PDU with IEC C19 outlets
APC Power Cord, C20 to IEC309 (16A), 2.5m. Cable length: 2.5 m. Input voltage: 230 V, Input current: 16 A

Features		Operational conditions	
Product colour *	Black	Operating altitude	0 - 3000 m
Connector 1 gender *	Male	Non-operating altitude	0 - 15000 m
Connector 2 gender *	Female	Weight & dimensions	
Cable length *	2.5 m	Weight	500 g
Power		Packaging data	
Input voltage	230 V	Package width	305 mm
Input current	16 A	Package height	102 mm
Operational conditions		Package weight	610 g
Operating temperature (T-T)	-10 - 40 °C	Logistics data	
Operating relative humidity (H-H)	20 - 80%	Harmonized System (HS) code	84733080
Storage relative humidity (H-H)	20 - 80%	Total carbon footprint (kg of CO2e)	157.72
		Other features	
		Dimensions (WxDxH)	292 x 95 x 95 mm



0731304252139



731304252139

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.