



APC NetShelter Cable Management, Data Cable Partition, Black, 747 x 122 x 72 mm

Brand : APCProduct code: AR8172BLK

Product name : APC NetShelter Cable Management, Data Cable Partition, Black, 747 x 122 x 72 mm

APC NetShelter Cable Management, Data Cable Partition, Black, 747 x 122 x 72 mm

APC NetShelter Cable Management, Data Cable Partition, Black, 747 x 122 x 72 mm:

The solid Partition AR8172BLK allows overhead routing of networking cables on top of the NetShelter enclosures and 4-post racks. Two partitions attach without tools to the roof in a variety of depths. The solid partition is designed to be mounted in the front for a clean look. Each partition ships with ground studs and one 8 inch/203mm grounding strap.
APC NetShelter Cable Management, Data Cable Partition, Black, 747 x 122 x 72 mm. Type: Cable duct, Product colour: Black. Weight: 2.27 kg

Features		Packaging data	
Type *	Cable duct	Package width	744 mm
Product colour *	Black	Package depth	165 mm
On/off switch	×	Package height	211 mm
Castor wheels	×	Package weight	3.64 kg
Locking	×	Technical details	
Weight & dimensions		Total carbon footprint (kg of CO2e)	11.04
Width	747 mm	Logistics data	
Depth	72 mm	Harmonized System (HS) code	85389099
Height	122 mm		
Weight	2.27 kg		



0731304199182




731304199182




7313041991828



4053162266728




5052217437440



0151903686652



151903686652



0132017921051




132017921051



0172302659832



172302659832



5051964576563

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.