APC 1U 19" Black Modular Toolless Airflow Management Blanking Panel - Qty 10

Brand : APC

Product code: AR8136BLK

Product name : 1U 19" Black Modular Toolless Airflow Management Blanking Panel - Qty 10

1U 19" Black Modular Toolless Airflow Management Blanking Panel - Qty 10

APC 1U 19" Black Modular Toolless Airflow Management Blanking Panel - Qty 10:

Modular toolless 1U Airflow Management Blanking Panel AR8136BLK to prevent air recirculation by occupying unused rack space (Qty 10).
APC 1U 19" Black Modular Toolless Airflow Management Blanking Panel - Qty 10. Type: Blank panel, Product colour: Black. Weight: 90 g

Features	
Type *	Blank panel
Product colour *	Black
Built-in fan	✕
Rack capacity	10U
On/off switch	✕
Castor wheels	✕
Locking	✕
Certification	REACH
Weight & dimensions	
Width	483 mm
Depth (max)	2.8 cm
Height	45 mm

Weight & dimensions	
Weight	90 g
Packaging data	
Package width	526 mm
Package depth	249 mm
Package height	105 mm
Package weight	1.64 kg
Technical details	
Total carbon footprint (kg of CO2e)	4.98
Compliance certificates	RoHS
Logistics data	
Harmonized System (HS) code	85389099



5051964197744



731304219200



0163121136956



7313042192002



168141423420

778888143040




132017749860

999992658200



763615802000



0172302660364

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date