



APC KVM-USBVM KVM cable Black

Brand : APC

Product code: KVM-USBVM

Product name : KVM-USBVM



KVM-USBVM - KVM 2G, Server Module, USB with Virtual Media

APC KVM-USBVM KVM cable Black:

Manage multiple servers with just one keyboard, monitor and mouse.

Out-of-band management

Troubleshoot servers and diagnose problems in lieu of a working operating system with POST and BIOS-level access to servers.


Scalable Architecture

Cascade multiple KVM switches for a modular solution that supports multiple platforms, improving flexibility and simplifying future expansion. Please see the user's manual for specific cascading capabilities.

Multi-platform Support

Windows, Sun, Unix and Linux compatible.
APC KVM-USBVM. Product colour: Black, Connector 1: D-Sub, USB, Connector 2: RJ-45. Weight: 130 g, Package depth: 129 mm, Package height: 42 mm. Depth: 125 mm, Height: 14 mm, Width: 125 mm

Performance		Packaging data	
Product colour	Black	Package weight	160 g
Connector 1	D-Sub, USB	Other features	
Connector 2	RJ-45	Depth	125 mm
Packaging data		Height	14 mm
Weight	130 g	Width	125 mm
Package depth	129 mm	Compatible operating systems	Windows, Sun, Unix, Linux
Package height	42 mm	Logistics data	
		Harmonized System (HS) code	84733080



0731304286691



731304286691

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.