



DELL 7TCDN network transceiver module Fiber optic 4000 Mbit/s QSFP+ 850 nm

Brand : DELL

Product code: 407-BBOZ

Product name : 7TCDN

40GbE QSFP+ SR, 850nm, 100 -150m, OM3/ OM4

DELL 7TCDN network transceiver module Fiber optic 4000 Mbit/s QSFP+ 850 nm:

The Dell™ QSFP+ transceiver delivers fiber connectivity to extend the range of your network. This hot-pluggable transceiver with QSFP+ (Quad Form Factor Pluggable) footprint features a MPO-12connector. The Dell networking 40GBase-SR4 QSFP+ transceiver provides 40GbE connectivity up to 100-150m.

Additionally, it provides a unique enhanced digital diagnostic monitoring interface, which allows real-time access to device operating parameters such as transceiver temperature, laser bias current, transmitted optical power, received optical power, and transceiver supply voltage.

DELL 7TCDN. SFP transceiver type: Fiber optic, Maximum data transfer rate: 4000 Mbit/s, Interface type: QSFP+. Brand compatibility: Dell, Compatible products: - Dell Networking N3132PX-ON - Dell Networking N4000 Series - Dell Networking N4032 - Dell.... Quantity per pack: 1 pc(s)

Performance	
SFP transceiver type *	Fiber optic
Maximum data transfer rate *	4000 Mbit/s
Interface type *	QSFP+
Fiber optic connector	LC
SFP transceiver standard	SR
Maximum transfer distance	150 m
Wavelength	850 nm
Features	
Brand compatibility	Dell



Features	
	- Dell Networking N3132PX-ON - Dell Networking N4000 Series - Dell Networking N4032 - Dell Networking N4032F - Dell Networking N4064 - Dell Networking N4064F - Dell Networking S4048-ON - Dell Networking S4048T-ON - Dell Networking S4810-ON - Dell Networking S5000 - Dell Networking S5212F-ON - Dell Networking S5224F-ON - Dell Networking S5232F-ON - Dell Networking S5248F-ON - Dell Networking S5296F-ON - Dell Networking S6100 - Dell Networking Z9100 - OptiPlex GX260 DT - PowerConnect 8100 - PowerConnect 8100 Series - PowerEdge C4130 - PowerEdge C4140 - PowerEdge C6320 - PowerEdge C6420 - PowerEdge FC420 - PowerEdge FC430 - PowerEdge FC620 - PowerEdge FC630 - PowerEdge FC640 - PowerEdge FC830 - PowerEdge M1000e - PowerEdge M640 - PowerEdge M640 VRTX - PowerEdge R200 - PowerEdge R220 - PowerEdge R230 - PowerEdge R240 - PowerEdge R300 - PowerEdge R320 - PowerEdge R330 - PowerEdge R340 - PowerEdge R410 - PowerEdge R415 - PowerEdge R420 - PowerEdge R430 - PowerEdge R440 - PowerEdge R510 - PowerEdge R515 - PowerEdge R520 - PowerEdge R530 - PowerEdge R540 - PowerEdge R610 - PowerEdge R620 - PowerEdge R630 - PowerEdge R640 - PowerEdge R6415 - PowerEdge R710 - PowerEdge R715 - PowerEdge R720 - PowerEdge R720XD - PowerEdge R730 - PowerEdge R730xd XL - PowerEdge R740 - PowerEdge R740XD - PowerEdge R740xd2 - PowerEdge R7415 - PowerEdge R7425 - PowerEdge R805 - PowerEdge R810 - PowerEdge R815 - PowerEdge R820 - PowerEdge R830 - PowerEdge R840 - PowerEdge R900 - PowerEdge R905 - PowerEdge R910 - PowerEdge R920 - PowerEdge R930 - PowerEdge R940 - PowerEdge R940xa - PowerEdge T130 - PowerEdge T140 - PowerEdge T330 - PowerEdge T340 - PowerEdge T410 - PowerEdge T420 - PowerEdge T430 - PowerEdge T440 - PowerEdge T610 - PowerEdge T620 - PowerEdge T630 - PowerEdge T640 - PowerEdge T710 - PowerEdge XR2 - PowerVault DL2100 - PowerVault DL2200 - PowerVault DR4100 - PowerVault NX3000 - PowerVault NX3200 - PowerVault NX3300 - PowerVault NX400 - PowerVault NX440
Compatible products	
Packaging content	
Quantity per pack	1 pc(s)
Logistics data	
Harmonized System (HS) code	85369010



5397063819539



0884116181835



884116181835

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.