APC Rack PDU, Basic, Zero U, 30A, 200/208V, (20)C13 & (4)C19



Brand : APC

Product code: AP7541

Product name : Rack PDU, Basic, Zero U, 30A, 200/208V, (20)C13 & (4)C19

Rack PDU, Basic, Zero U, 30A, 200/208V, (20)C13 & (4)C19

APC Rack PDU, Basic, Zero U, 30A, 200/208V, (20)C13 & (4)C19:

APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit
APC Rack PDU, Basic, Zero U, 30A, 200/208V, (20)C13 & (4)C19. Product colour: Black. Input connection type: NEMA L6-30P, Output connections: (20) IEC 320 C13 (4) IEC 320 C19. Cable length: 3.05 m. Nominal input voltage: 208 V, AC input frequency: 50 - 60 Hz, Load capacity: 4992 VA. Certification: cUL,CSA C22.2 No. 60950-1-03,METI Denan,UL 60950-1,UL



0731304225560



731304225560

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date