

StarTech.com 8in EPS 8 Pin Power Extension Cable

Brand : StarTech.com

Product code: EPS8EXT

Product name : 8in EPS 8 Pin Power Extension Cable

StarTech.com 8in EPS 8 Pin Power Extension Cable

StarTech.com 8in EPS 8 Pin Power Extension Cable:

Extend the reach of your EPS power supply cable by 8in

The EPS8EXT EPS Power Extension Cable features one female and one male 8-pin ATX 12V connector, enabling you to extend the reach of your EPS power supply cable by up to 8-inches and giving you the flexibility to custom build your PC without having to stretch or strain the cable.

Designed and constructed to provide a dependable connection, the EPS8EXT is backed by StarTech.com’s lifetime warranty.

The StarTech.com Advantage

- Guaranteed reliability

StarTech.com 8in EPS 8 Pin Power Extension Cable. Connector 1: 8-pin EPS12V, Connector 2: 8-pin EPS12V, Cable length: 0.203 m. Compliance certificates: RoHS, Certification: CE, REACH. Width: 18 mm, Height: 24 mm, Weight: 20 g. Package width: 128 mm, Package height: 220 mm, Package weight: 28 g

| Features                |              | Certificates                |           |
|-------------------------|--------------|-----------------------------|-----------|
| Cable length *          | 0.203 m      | Certification               | CE, REACH |
| Connector 1 *           | 8-pin EPS12V | Weight & dimensions         |           |
| Connector 2 *           | 8-pin EPS12V | Width                       | 18 mm     |
| Connector 1 gender      | Male         | Height                      | 24 mm     |
| Connector 2 gender      | Female       | Weight                      | 20 g      |
| Connector 1 form factor | Straight     | Packaging data              |           |
| Connector 2 form factor | Straight     | Package width               | 128 mm    |
| Product colour          | Yellow       | Package height              | 220 mm    |
| Certificates            |              | Package weight              | 28 g      |
| Compliance certificates | RoHS         | Logistics data              |           |
|                         |              | Harmonized System (HS) code | 84733080  |





0065030821728



065030821728



5054533088825

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.