

StarTech.com 16in 9 Pin Serial Male to 10 Pin Motherboard Header Panel Mount Cable

Brand : StarTech.com

Product code: PNL9M16

Product name : 16in 9 Pin Serial Male to 10 Pin Motherboard Header Panel Mount Cable

StarTech.com 16in 9 Pin Serial Male to 10 Pin Motherboard Header Panel Mount Cable - motherboard to RS232

StarTech.com 16in 9 Pin Serial Male to 10 Pin Motherboard Header Panel Mount Cable:

Turn a Motherboard IDC Serial Header into a Panel-Mountable 9-Pin RS232 Serial Connector

The PNL9M16 16-inch IDC Serial to Panel Mount Serial Cable, features a 10-pin (IDC) motherboard header connection on one end and a panel mount DB9 male connector port on the other - a simple answer for adding a DB9 (RS232) serial port to any computer system which has an RS232 serial panel mount receptacle.

This cost-effective solution bridges the compatibility gap between modern computers and legacy serial peripherals.

The StarTech.com Advantage

- Extend the Motherboard IDC Serial Interface to an RS232 serial panel mount receptacle
- Combine legacy products with newer technology to satisfy all your business requirements
- Backed by the StarTech.com lifetime warranty

Features		Packaging data	
Product colour *	Grey	Package width	128 mm
Cable length *	0.4064 m	Package height	220 mm
Connector 1 *	DB-9	Package weight	22 g
Connector 2 *	IDC	Certificates	
Connector 1 gender	Male	Certification	CE, REACH, RoHS
Connector 2 gender	Female	Weight & dimensions	
AWG wire size	28	Weight	17 g
Packaging data		Logistics data	
Quantity per pack	1 pc(s)	Harmonized System (HS) code	84733080





0065030844604



065030844604



0132017557953



132017557953



0650308446040



650308446040

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.