



APC Netshelter CX 18U Freestanding rack Oak

Brand : APC
Product code: AR4018IA
Product name : Netshelter CX 18U

18U, 750 x 1130 x 1015 mm, 138 kg, 200 - 230 VAC, 50/60 Hz

APC Netshelter CX 18U Freestanding rack Oak:


NetShelter CX 18U Secure Soundproof Server Room in a Box Enclosure International
Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Includes: Casters, Key(s), Leveling feet, Rack Power Distribution Unit (PDU), Side Panels, Unpacking sheet
APC Netshelter CX 18U. Type: Freestanding rack, Rack capacity: 18U, Maximum weight capacity: 830 kg. Weight: 138 kg. Product colour: Oak



Features		Weight & dimensions	
Rack capacity *	18U	Size (imperial)	48.3 cm (19")
Type *	Freestanding rack	Width	750 mm
Maximum weight capacity *	830 kg	Depth	1130 mm
Product colour	Oak	Height	1015 mm
Cooling type	Active	Weight	138 kg
Certification	EN 60950,UL 60950-1 RoHS,REACH: Contains No SVHCs	Packaging data	
Power		Package weight	170 kg
AC input voltage	200 - 230 V	Logistics data	
AC input frequency	50 - 60 Hz	Harmonized System (HS) code	85381000
		Other features	
		Package dimensions (WxDxH)	800 x 1200 x 1250 mm
		Power requirements	AC 200 - 230V, 50/60 Hz



0731304300250



731304300250



0731304271253



731304271253

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.