

StarTech.com 3 ft Panel Mount USB Cable A to A - F/M

Brand : StarTech.com

Product code: USBPNLAFAM3

Product name : 3 ft Panel Mount USB Cable A to A - F/M

StarTech.com 3 ft Panel Mount USB Cable A to A F/M - Panel Mount USB Extension USB A-Female to A-Male Adapter Cable 3ft - USB-A (F) Port
StarTech.com 3 ft Panel Mount USB Cable A to A - F/M. Cable length: 0.9 m. Connector 1: USB A, Connector 2: USB A, USB version: USB 2.0, Connector contacts plating: Nickel, Product colour: Black




Features		Weight & dimensions	
USB version *	USB 2.0	Cable length *	0.9 m
Connector 1 *	USB A	Weight	40 g
Connector 2 *	USB A	Packaging data	
Connector 1 gender *	Male	Package width	125 mm
Connector 2 gender *	Female	Package depth	225 mm
Connector 1 form factor	Straight	Package height	14 mm
Connector 2 form factor	Straight	Package weight	46 g
AWG wire size	24/28	Packaging content	
Connector contacts plating	Nickel	Quantity per pack *	1 pc(s)
Cable jacket material	Polyvinyl chloride (PVC)	Certificates	
Cable shielding	Aluminum mylar foil	Compliance certificates	RoHS
Plug and Play	✓	Certification	CE, REACH
Product colour *	Black	Logistics data	
		Harmonized System (HS) code	84733080



0065030852111



065030852111



0785307913849



785307913849

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.