

StarTech.com Thunderbolt 3 Cable - 20Gbps - 1m - White - Thunderbolt, USB, and DisplayPort Compatible

Brand : StarTech.com

Product code: TBLT3MM1MW

Product name : Thunderbolt 3 Cable - 20Gbps - 1m - White - Thunderbolt, USB, and DisplayPort Compatible

StarTech.com 3.3ft (1m) Passive Thunderbolt 3 Cable, 20Gbps, 100W PD, 4K Video, Thunderbolt Cable, Compatible with USB4/DP Alt Mode, Thunderbolt 4, USB 3.2/Type-C (TBLT3MM1MW)
StarTech.com Thunderbolt 3 Cable - 20Gbps - 1m - White - Thunderbolt, USB, and DisplayPort Compatible. Connector 1: Male, Connector 2: Male, Cable length: 1 m. Compliance certificates: RoHS. Weight: 42 g. Quantity per pack: 1 pc(s), Package width: 125 mm, Package depth: 225 mm. Products per master (outer) case: 60 pc(s), Master (outer) case length: 442 mm, Master (outer) case width: 299 mm



Features		Packaging data	
Connector 1 *	Male	Quantity per pack	1 pc(s)
Connector 2 *	Male	Package width	125 mm
Cable length *	1 m	Package depth	225 mm
Data transfer rate (max) *	20 Gbit/s	Package height	12 mm
Product colour *	White	Package weight	50 g
Thunderbolt version *	3	Logistics data	
Maximum resolution	3840 x 2160 pixels	Products per master (outer) case	60 pc(s)
Jacket material	Polyvinyl chloride (PVC)	Master (outer) case length	442 mm
Certificates		Master (outer) case width	299 mm
Compliance certificates	RoHS	Master (outer) case height	205 mm
Weight & dimensions		Harmonized System (HS) code	84733080
Weight	42 g		



0065030871273



065030871273

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.