

StarTech.com 36in SATA Serial ATA Cable

Brand : StarTech.com

Product code: SATA36

Product name : 36in SATA Serial ATA Cable



StarTech.com 36in SATA Serial ATA Cable

StarTech.com 36in SATA Serial ATA Cable:

Connect and position SATA drives easily - designed for larger cases

The SATA36 Serial ATA Cable features two 7-pin data receptacles and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance and reliability this 36" SATA cable is backed by our lifetime warranty.

The StarTech.com Advantage

- Features a thin cable design, which helps reduce clutter and increase airflow within the computer/server case, for optimum system performance
- Backed by StarTech.com lifetime warranty, ensuring a dependable connection

Features		Certificates	
Cable length *	0.914 m	Compliance certificates	RoHS
Cable type *	SATA III	Packaging data	
Connector 1 *	SATA 7-pin	Package width	128 mm
Connector 2 *	SATA 7-pin	Package depth	0.7 mm
Connector 1 form factor	Straight	Package height	220 mm
Connector 2 form factor	Straight	Package weight	250 g
Connector gender *	Female/Female	Technical details	
Product colour *	Red	Connector(s)	SATA Data 7 pin Female / SATA Data 7 pin Female
Weight	26 g	Logistics data	
		Harmonized System (HS) code	84733080




0065030796002



065030796002



9789792276848



5051964492009

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.