



APC NetShelter Cable Management, Data Cable Partition, Pass Through, Black, 579 x 122 x 71 mm

Brand : APC

Product code: AR8163ABLK

Product name : APC NetShelter Cable Management, Data Cable Partition, Pass Through, Black, 579 x 122 x 71 mm

APC NetShelter Cable Management, Data Cable Partition, Pass Through, Black, 579 x 122 x 71 mm

APC NetShelter Cable Management, Data Cable Partition, Pass Through, Black, 579 x 122 x 71 mm:

The pass-through Partition AR8163ABLK allows overhead routing of networking cables on top of the NetShelter enclosures and 4-post racks. Two Partitions attach without tools to the roof in a variety of depths. The pass-through Partition is designed with a cable access hole to facilitate routing cables. Each partition ships with ground studs and one 8 inch/203mm grounding strap.
APC NetShelter Cable Management, Data Cable Partition, Pass Through, Black, 579 x 122 x 71 mm.
Type: Cable duct, Product colour: Black. Weight: 1.82 kg


Features		Packaging data	
Type *	Cable duct	Package width	610 mm
Product colour *	Black	Package depth	178 mm
Built-in fan	✗	Package height	203 mm
On/off switch	✗	Package weight	2.73 kg
Castor wheels	✗	Technical details	
Locking	✗	Total carbon footprint (kg of CO2e)	8.28
Weight & dimensions		Compliance certificates	RoHS
Width	597 mm	Logistics data	
Depth (max)	7.1 cm	Harmonized System (HS) code	85389099
Height	122 mm		
Weight	1.82 kg		



0731304194859



731304194859



5051749235487



7313041948594



4053162514584

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.