

StarTech.com 60x20mm Replacement Ball Bearing Computer Case Fan w/ TX3 Connector

Brand : StarTech.com

Product code: FAN6X2TX3

Product name : 60x20mm Replacement Ball Bearing Computer Case Fan w/ TX3 Connector

StarTech.com 60x20mm Replacement Ball Bearing Computer Case Fan w/ TX3 Connector - 3 pin case Fan - TX3 Fan - 60mm Fan
StarTech.com 60x20mm Replacement Ball Bearing Computer Case Fan w/ TX3 Connector. Type: Fan, Fan diameter: 6 cm, Rotational speed (max): 4500 RPM. Voltage: 12 V. Width: 20 mm, Depth: 60 mm, Height: 60 mm. Product colour: Black




Performance		Weight & dimensions	
Suitable location *	Computer case	Height	60 mm
Type *	Fan	Weight	38 g
Fan diameter	6 cm	Package width	66 mm
Rotational speed (max)	4500 RPM	Package depth	115 mm
Noise level (high speed)	28 dB	Package height	31 mm
Maximum airflow	21.46 cfm	Package weight	67 g
Operating temperature (T-T)	-10 - 80 °C	Technical details	
Design		Bearing technology	Ball bearing
Product colour *	Black	Compliance certificates	RoHS
Material	Plastic	Other features	
Number of fans	1 fan(s)	Dimensions (WxDxH)	60 x 60 x 20 mm
Power		Connector(s)	1 - TX3 Female
Voltage	12 V	Airflow	22.1
Weight & dimensions		Rotational speed	4500 RPM
Width	20 mm	Logistics data	
Depth	60 mm	Harmonized System (HS) code	84733080




0065030786591



065030786591



5051964166948



3609740153105

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.