

ZYXEL


Zyxel SFP-SX-D network transceiver module 1000 Mbit/s 850 nm

Brand : Zyxel
Product code: 91-010-204001B
Product name : SFP-SX-D

1000Base-LHX SFP Transceiver, IEEE 802.3z
Zyxel SFP-SX-D. Maximum data transfer rate: 1000 Mbit/s, Maximum transfer distance: 550 m,
Wavelength: 850 nm. Form factor: Plug-in. Safety: Class 1 Laser, CSA, TUV, 21 CFR 1040.10 & 1040.11.
Width: 56 mm, Depth: 13.4 mm, Height: 12.5 mm. Dimensions (WxDxH): 56 x 13.4 x 12.46 mm



Performance		Operational conditions	
Maximum data transfer rate *	1000 Mbit/s	Storage temperature (T-T)	-40 - 85 °C
Maximum transfer distance	550 m	Operating relative humidity (H-H)	5 - 95%
Wavelength	850 nm	Weight & dimensions	
Cabling technology	1000Base-LHX	Width	56 mm
Features		Depth	13.4 mm
Form factor	Plug-in	Height	12.5 mm
Certificates		Other features	
Safety	Class 1 Laser, CSA, TUV, 21 CFR 1040.10 & 1040.11	Dimensions (WxDxH)	56 x 13.4 x 12.46 mm
Operational conditions		Logistics data	
Operating temperature (T-T)	0 - 70 °C	Harmonized System (HS) code	85369010



4718937510344

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.