

ZYXEL

Zyxel XGS4600-52F Managed L3 Black

Brand : Zyxel

Product code: XGS4600-52F-ZZ0101F

Product name : XGS4600-52F

XGS4600-52F - 48-port GbE L3 Managed Fiber Switch with 4 SFP+ Uplink

Zyxel XGS4600-52F Managed L3 Black:

Stylish Outlook

New ID design with carbon fiber look name plate delivers the modern look-and-feel in the closet.
Choose a right L3 switch for your network

High Availability

The XGS4600 Series comes with Gigabit connectivity and four integrated 10-Gigabit SFP+ slots that enable high-speed uplink connections for affordable, reliable network elements.

Stacking Capability

The XGS4600-32/32F allows creating a physical stack through one or two 10-Gigabit SFP+ slots.
XGS4600 series features dynamic routing to simplify cross-subnet communications for businesses such as hospitality venues and education institutions that operate complex networks.

High Resiliency

The XGS4600 Series is designed to support active-standby power redundancy to trigger backup power supply to take over in case the main power supply fails.

Management features		Performance	
Switch type *	Managed	Noise level	42.6 dB
Switch layer	L3	Mean time between failures (MTBF)	815860 h
Web-based management	✓	Power	
Ports & interfaces		AC input voltage	100 - 240 V
SFP module slots quantity	48	AC input frequency	50 - 60 Hz
SFP+ module slots quantity	4	Power consumption (max)	70.16 W
Network		Power over Ethernet (PoE)	
Networking standards *	IEEE 802.1D, IEEE 802.1Q, IEEE 802.1p, IEEE 802.1s, IEEE 802.1w, IEEE 802.1x, IEEE 802.3, IEEE 802.3ab, IEEE 802.3ad, IEEE 802.3az, IEEE 802.3u, IEEE 802.3x	Power over Ethernet (PoE) *	✗
10G support *	✓	Operational conditions	
IP routing	✓	Operating temperature (T-T)	0 - 50 °C
Data transmission		Storage temperature (T-T)	-40 - 70 °C
Switching capacity *	176 Gbit/s	Operating relative humidity (H-H)	10 - 95%
MAC address table *	32000 entries	Storage relative humidity (H-H)	10 - 95%
Packet buffer memory	4 MB	Heat dissipation	252.68 BTU/h
Security		Weight & dimensions	
DHCP features	DHCP server	Width	441 mm
Access Control List (ACL)	✓	Depth	360 mm
Security algorithms	SSH, SSL/TLS	Height	44 mm
MAC address filtering	✓	Weight	4.97 kg
SSH/SSL support	✓	Packaging data	
BPDU filtering/protection	✓	Package width	616 mm
		Package depth	355 mm
		Package height	107 mm
		Package weight	6.6 kg
		Logistics data	
		Harmonized System (HS) code	85176990

Design	
Rack mounting *	✓
Stackable *	✗
Product colour	Black
LED indicators	✓
Performance	
Internal memory	1024 MB
Flash memory	64 MB



4718937595570

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.