APC Battery Replacement Cartridge APCRBC163 (OEM)

Brand : APC

Product code: APCRBC163

Product name : Battery Replacement Cartridge APCRBC163 (OEM)



- Brand new battery shipped from strictly managed warehouse
- Leak-proof sealed lead-acid battery
- Fully assembled and ready for use
- Supports APC-authorized recycling for earth-friendly disposal
- "lead-acid battery"

Battery Replacement Cartridge APCRBC163 (OEM)

APC Battery Replacement Cartridge APCRBC163 (OEM):

This APC Replacement Battery Cartridge is specifically designed to be fully compatible with APC Back-UPS. The 12V 9.4Ah VRLA battery is thoroughly tested to restore the UPS performance to its original specifications. The APCRBC163 battery comes with a 2-year repair or replaceable warranty.
APC Battery Replacement Cartridge APCRBC163 (OEM). Battery technology: Sealed Lead Acid (VRLA), Battery life: 35 year(s), Product colour: Black. Compliance certificates: RoHS. Weight: 5.85 kg, Width: 66 mm, Height: 302 mm. Package width: 185 mm, Package height: 417 mm, Package depth: 180 mm

Features	
Battery technology *	Sealed Lead Acid (VRLA)
Battery life	35 year(s)
Product colour	Black
Certificates	
Compliance certificates	RoHS
Sustainability	
Sustainability compliance	✔
Weight & dimensions	
Weight	5.85 kg

Weight & dimensions	
Width	66 mm
Height	302 mm
Depth	109 mm
Packaging data	
Package width	185 mm
Package height	417 mm
Package depth	180 mm
Package weight	6300 kg
Logistics data	
Harmonized System (HS) code	85044095



0731304336013



731304336013

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date