Targus

Targus Cypress EcoSmart 35.6 cm (14") Sleeve case Grey



Brand : Targus

Product code: TBS64602GL

Product name : Cypress EcoSmart

- Made from 3 recycled plastic water bottles
- Foam laptop protection
- Plush interior protects device from scuffs and scratches
Cypress 13-14” Sleeve with EcoSmart, Grey

Targus Cypress EcoSmart 35.6 cm (14") Sleeve case Grey:



Made from recyclable materials on the inside and out. Using fabric woven from 3 recycled plastic water bottles, the 13-14” Cypress Sleeve with EcoSmart® is thoughtfully designed to protect your laptop while also protecting the environment. Slim and lightweight, this sleeve protects your laptop, while being wrapped up in sleek and sophisticated eco-conscious material.
Targus Cypress EcoSmart. Case type: Sleeve case, Maximum screen size: 35.6 cm (14"). Weight: 90 g.
Surface coloration: Monochromatic

Features	
Surface coloration	Monochromatic
Maximum screen size *	35.6 cm (14")
Case type *	Sleeve case
Product main colour *	Grey
Brand compatibility *	Any brand
Protection features	Scratch resistant
Country of origin	China

Features	
Quantity	1
Weight & dimensions	
Width	965 mm
Depth	63.5 mm
Height	760 mm
Weight	90 g
Logistics data	
Harmonized System (HS) code	84733080

5051794029949

0092636344917

092636344917

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date