



Lenovo 2.8m, 10A/100-250V, C13 to IEC 320-C14 Rack

Brand : Lenovo

Product code: 4L67A08366

Product name : 2.8m, 10A/100-250V, C13 to IEC 320-C14 Rack




2.8m, 10A/100-250V, C13 to IEC 320-C14 Rack

Lenovo 2.8m, 10A/100-250V, C13 to IEC 320-C14 Rack:

- Cord Length: 9 ft
- Connector on First End: 3-pin IEC 60320 C13 Female
- Connector on Second End: 3-pin IEC 60320 C14 Male
- Current Rating: 10A

Lenovo 2.8m, 10A/100-250V, C13 to IEC 320-C14 Rack. Cable length: 2.8 m, Connector 1: C13 coupler, Connector 2: C14 coupler. Input voltage: 100 - 250 V, Input current: 10 A

Features		Features	
Product colour *	Black	Connector 2 form factor	Straight
Connector 1 gender *	Female		ThinkSystem
Connector 2 gender *	Male	Compatibility	DB620/SD530/SR530/SR550/SR630, SR650/SR850/SR950/ST550
Cable length *	2.8 m	Power	
Connector 1 *	C13 coupler	Input voltage	100 - 250 V
Connector 2 *	C14 coupler	Input current	10 A
Connector 1 standard	IEC 60320	Packaging data	
Connector 2 standard	IEC 60320	Quantity per pack	1 pc(s)
Connector 1 form factor	Straight	Logistics data	
		Harmonized System (HS) code	84733080



0889488436811



889488436811

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.