APC Battery Replacement Cartridge RBC57 (OEM)

Brand : APC

Product code: RBC57

Product name : Battery Replacement Cartridge RBC57 (OEM)



- 12V 9AH replaceable battery for APC Smart-UPS BS
- Brand new battery shipped from strictly managed warehouse
- Peace of mind with 2-year warranty and UPS safety certifications
- Supports APC-authorized recycling for earth-friendly disposal
- lead-acid battery

Battery Replacement Cartridge RBC57 (OEM)

APC Battery Replacement Cartridge RBC57 (OEM):

The genuine APC Replacement Battery Cartridge (RBC) is tested and certified for 100% compatibility to the the specific APC UPS. This lead-acid RBC has a lifetime of three to five years which offers reliable support and extends the useful life of your UPS. The APC RBC comes fully assembled and ready for use. To see the compatible UPS list, please click View Compatible UPS Modelsbutton in Get Support Section at APC.com

APC Battery Replacement Cartridge RBC57 (OEM). Battery technology: Lead acid, Number of batteries included: 1 pc(s), Battery life: 3 year(s). Weight: 11.2 kg, Width: 165 mm, Height: 70 mm

Features		Operational conditions	
Battery technology *	Lead acid	Operating temperature (T-T)	0 - 40 °C
Number of batteries included *	1 pc(s)	Storage temperature (T-T)	-15 - 45 °C
Battery life	3 year(s)	Operating relative humidity (H-H)	0 - 95%
Product colour	Black	Storage relative humidity (H-H)	0 - 95%
Weight & dimensions		**Logistics data**	
Weight	11.2 kg	Harmonized System (HS) code	85044095
Width	165 mm	Total carbon footprint (kg of CO2e)	41.33
Height	70 mm		
Depth	419 mm		



0731304228479



731304228479

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date