



APC GVSBPSU10K20H UPS accessory

Brand : APC

Product code: GVSBPSU10K20H

Product name : GVSBPSU10K20H

Galaxy VS Maintenance Bypass Panel, single unit, 10-20kW 400V wallmount

APC GVSBPSU10K20H UPS accessory:

Galaxy VS Maintenance Bypass Panel, single unit, 10-20kW 400V wallmount
Maintenance bypass panel for complete isolation of the UPS during service operations.
APC GVSBPSU10K20H. Product type: Bypass switch, Mounting type: Wall-mount, Product colour: White.
Compliance certificates: RoHS, Certification: REACH. Width: 400 mm, Depth: 150 mm, Height: 450 mm.
Quantity per pack: 1 pc(s). Package width: 260 mm, Package depth: 590 mm, Package height: 537 mm



Features		Weight & dimensions	
Product type *	Bypass switch	Height	450 mm
Mounting type	Wall-mount	Weight	12 kg
Product colour	White	Packaging content	
Easy to use	✓	Quantity per pack	1 pc(s)
Easy to install	✓	Packaging data	
Certificates		Package width	260 mm
Compliance certificates	RoHS	Package depth	590 mm
Certification	REACH	Package height	537 mm
Weight & dimensions		Package weight	22 kg
Width	400 mm	Logistics data	
Depth	150 mm	Harmonized System (HS) code	85079080



0731304367406



731304367406

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.